Product data sheet

Specifications







PUSH BUTTON 600VAC 10A 30MM T-K

9001K3L38LYYH5

() Discontinued on: Jul 1, 2020



Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated push-button	
Device Short Name	К	
Type Of Operator	spring return	
Operator Profile	Yellow flush	
Operator Additional Information	Extended metallic guard	

Complementary

Bezel MaterialChromium plated metalMounting Diameter1.18 in (30 mm)Light SourceLEDBulb BaseBA 9sLight Block SupplyDirect[Us] Rated Supply Voltage120 V AC/DCContacts Type And Composition1 NOConnections - TerminalsScrew clamp terminalsOperating PositionAny position[le] Rated Operational Current10 A, AC-15 10 A, DC-13Contact OperationStandardDevice PresentationComplete product		
Light Source LED Bulb Base BA 9s Light Block Supply Direct [Us] Rated Supply Voltage 120 V AC/DC Contacts Type And Composition 1 NO Connections - Terminals Screw clamp terminals Operating Position Any position [Ie] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Bezel Material	Chromium plated metal
Bulb Base BA 9s Light Block Supply Direct [Us] Rated Supply Voltage 120 V AC/DC Contacts Type And Composition 1 NO Connections - Terminals Screw clamp terminals Operating Position Any position [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Mounting Diameter	1.18 in (30 mm)
Light Block Supply Direct [Us] Rated Supply Voltage 120 V AC/DC Contacts Type And Composition 1 NO Connections - Terminals Screw clamp terminals Operating Position Any position [Ie] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Light Source	LED
[Us] Rated Supply Voltage 120 V AC/DC Contacts Type And Composition 1 NO Connections - Terminals Screw clamp terminals Operating Position Any position [Ie] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Bulb Base	BA 9s
Contacts Type And Composition 1 NO Connections - Terminals Screw clamp terminals Operating Position Any position [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Light Block Supply	Direct
Connections - Terminals Screw clamp terminals Operating Position Any position [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	[Us] Rated Supply Voltage	120 V AC/DC
Operating Position Any position [le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Contacts Type And Composition	1 NO
[le] Rated Operational Current 10 A, AC-15 10 A, DC-13 Contact Operation Standard	Connections - Terminals	Screw clamp terminals
10 Å, DC-13 Contact Operation Standard	Operating Position	Any position
	[Ie] Rated Operational Current	
Device Presentation Complete product	Contact Operation	Standard
	Device Presentation	Complete product

Environment

Product Certifications	NEMA UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03 CE
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Ordering and shipping details

Category	21426-9001 K (NOT KA,KM,KX)	
Discount Schedule	CS1	
Returnability	No	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin

MX

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov