# Product data sheet





# illuminated selector switch Ø 30 amber - 3 position - stay put - 24 V AC/DC

9001K43J35LYFA

Discontinued on: May 6, 2021



Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

| Range Of Product          | Harmony 9001K               |
|---------------------------|-----------------------------|
| Product Or Component Type | Illuminated selector switch |
| Device Short Name         | 9001K                       |
| Type Of Operator          | stay put                    |
| Operator Profile          | Red long handle             |

## Complementary

| Bezel Material                | Chromium plated metal  |
|-------------------------------|------------------------|
| Mounting Diameter             | 1.18 in (30 mm)        |
| Net Weight                    | 0.54 lb(US) (0.245 kg) |
| Shape Of Signaling Unit Head  | Octagonal              |
| Operator Position Information | 3 positions            |
| Contacts Type And Composition | Without contact block  |
| Mechanical Durability         | 500000 cycles          |
| Light Block Supply            | Direct                 |
| Light Source                  | LED                    |
| Bulb Base                     | BA 9s                  |
| Light Block Colour            | Amber                  |
| [Us] Rated Supply Voltage     | 24 V AC/DC             |
| Product Compatibility         | 9001KA1 side 1 or 2    |
| Device Presentation           | Basic element          |

#### **Environment**

| Protective Treatment                     | TC                   |
|--|----------------------|
| Ambient Air Temperature For Storage      | -40158 °F (-4070 °C) |
| Ambient Air Temperature For<br>Operation | -13158 °F (-2570 °C) |
| Electrical Shock Protection Class        | Class II IEC 61140   |
| Ip Degree Of Protection                  | IP66 IEC 60529       |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Nema Degree Of Protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 3R NEMA 4  |
|---------------------------|--|
| Standards                 | JIS C 4520<br>JIS C 852<br>EN/IEC 60947-1<br>EN/IEC 60947-5-4<br>EN/IEC 60947-5-1<br>CSA C22.2 No 14<br>UL 508 |
| Product Certifications    | UL 508<br>NEMA   |
| Vibration Resistance      | 7 gn 2500 Hz)IEC 60068-2-6   |
| Shock Resistance          | 50 gn IEC 60068-2-27   |

# Ordering and shipping details

| Category          | US10CS121426  |
|-------------------|---------------|
| Discount Schedule | 0CS1          |
| Gtin              | 3389118042957 |
| Returnability     | No            |
| Country Of Origin | MX            |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | China RoHS declaration  |
| Environmental Disclosure  | Product Environmental Profile   |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.  |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |