Product data sheet

Specifications



selector switch Ø 30 - 3 positions spring return - incandescent

9001K53J35FG

() Discontinued on: Dec 2, 2020

(!) End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001K	
Product Or Component Type	Illuminated selector switch	
Device Short Name	9001K	
Type Of Operator	Both sides to centre spring return	
Operator Profile	Green gloved hand knob	

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.54 lb(US) (0.245 kg)
Shape Of Signaling Unit Head	Round
Operator Position Information	3 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Direct
Light Source	incandescent
Bulb Base	BA 9s
[Us] Rated Supply Voltage	2428 V AC/DC
Device Presentation	Basic element

Environment

Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Electrical Shock Protection Class	Class II IEC 61140	
Ip Degree Of Protection	IP66 IEC 60529	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 6
Standards	EN/IEC 60947-1
	EN/IEC 60947-5-4
	JIS C 852
	JIS C 4520
	UL 508
	CSA C22.2 No 14
	EN/IEC 60947-5-1
Product Certifications	NEMA
	UL 508
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	US10CS121426	
Discount Schedule	0CS1	
Gtin	00785901932284	
Returnability	No	
Country Of Origin	МХ	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov