# Product data sheet

Specifications





# 30mm Push Button, Type K, push button, full guard, black, 1 NO and 1 NC

9001KR1BH13

Product availability: Stock - Normally stocked in distribution facility

## Price\*: 89.00 USD

## Main

Range Of Product	Harmony 9001K
Product Or Component Type	Push-button
Device Short Name	9001K
Type Of Operator	spring return
Operator Profile	Black flush, unmarked
Operator Additional Information	Metal guard

## Complementary

Bezel Material	Metal			
Mounting Diameter	1.18 in (30 mm)			
Shape Of Signaling Unit Head	Octagonal			
Contacts Type And Composition	1 C/O			
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm <sup>2</sup> IEC 60947-1			
Tightening Torque	7.08 lbf.in (0.8 N.m) IEC 60947-1			
Shape Of Screw Head	Cross slotted			
Mechanical Durability	5000000 cycles			
Operating Position	Any position			
[le] Rated Operational Current	3 A 240 V, AC-15, A600-Q600 NEMA 0.55 A 125 V, DC-13, A600-Q600 NEMA			
[Ui] Rated Insulation Voltage	250 V 3)IEC 60947-1			
[Uimp] Rated Impulse Withstand Voltage	2.5 kV IEC 60947-1			
Contacts Material	Silver alloy contacts			
Contact Operation	Standard			
Positive Opening	Without			
Short-Circuit Protection	10 A cartridge fuse IEC 60947-5-1			
[Ith] Conventional Free Air Thermal Current	10 A			
[Icm] Rated Short-Circuit Making Capacity	12 kA 600 V AC-15, 7200 VA 15 kA 480 V AC-15, 7200 VA 30 kA 240 V AC-15, 7200 VA 60 kA 120 V AC-15, 7200 VA 0.1 kA 600 V DC-13 0.27 kA 250 V DC-13 0.55 kA 125 V DC-13			

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Rated Breaking Capacity	3 kA 240 V AC-15, 720 VA
	6 kA 120 V AC-15, 720 VA
	1.2 kA 600 V AC-15, 720 VA
	1.5 kA 480 V AC-15, 720 VA
	0.1 kA 600 V DC-13
	0.27 kA 250 V DC-13
	0.55 kA 125 V DC-13
Terminals Description Iso N°1	(13-14-11-12)OF
Cad Overall Width	1.89 in (48 mm)
Cad Overall Height	1.77 in (45 mm)
Cad Overall Depth	2.20 in (56 mm)
Net Weight	0.27 lb(US) (0.121 kg)
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Black
Operator Profile	Flush
Type Of Operator	Spring return
Size	30 mm

## Environment

Standards	JIS C 852 UL 508 EN/IEC 60947-5-1 JIS C 4520 CSA C22.2 No 14 EN/IEC 60947-5-4 EN/IEC 60947-1
Product Certifications	UL 508 NEMA
Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

# Ordering and shipping details

Category	US10CS121426
Discount Schedule	0CS1
Gtin	785901066798
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.05 in (5.200 cm)
Package 1 Width	2.20 in (5.600 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	4.51 oz (128.000 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	5.91 in (15.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	4.96 lb(US) (2.248 kg)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance



Rohs Exemption Information


## **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

## **Product data sheet**

#### **Dimensions Drawings**

#### Dimensions




e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

#### Mounting and Clearance

### Contact Block Mounting Position

Top and Rear views




- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

# Product data sheet

#### Panel Cut-Out

#### Clearance



Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

#### Individual Cut-outs Details

2 alternatives

