# Product data sheet

Specifications





Illuminated push-button head, Harmony 9001SK, plastic, plastic guard flush, green, 30mm, spring return, LED green, 120V

9001SK1L38LGG

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 167.00 USD

#### Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001SK
Type Of Operator	spring return
Operator Profile	Green flush, unmarked
Operator Additional Information	Plastic guard
Light Block Supply	Direct 120 V AC/DC

#### Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Shape Of Signaling Unit Head	Octagonal
Light Source	Green LED
Bulb Base	BA 9s
[Us] Rated Supply Voltage	120 V AC/DC
Contacts Type And Composition	Without contact block
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm <sup>2</sup> EN/IEC 60947-1
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1
Shape Of Screw Head	Cross slotted
Mechanical Durability	5000000 cycles
Operating Position	Any position
[le] Rated Operational Current	0.55 A 125 V, DC-13, A600-Q600 NEMA
[Ui] Rated Insulation Voltage	250 V 3)EN/IEC 60947-1
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1
Positive Opening	Without
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1
[Ith] Conventional Free Air Thermal Current	10 A

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Life Is On Schneider

[Icm] Rated Short-Circuit Making	12 kA 600 V AC-15, 7200 VA
Capacity	15 kA 480 V AC-15, 7200 VA
	30 kA 240 V AC-15, 7200 VA
	60 kA 120 V AC-15, 7200 VA
	0.27 kA 250 V DC-13
	0.55 kA 125 V DC-13
	0.1 kA 600 V DC-13
Rated Breaking Capacity	1.2 kA 600 V AC-15, 720 VA
	1.5 kA 480 V AC-15, 720 VA
	3 kA 240 V AC-15, 720 VA
	6 kA 120 V AC-15, 720 VA
	0.27 kA 250 V DC-13
	0.55 kA 125 V DC-13
	0.1 kA 600 V DC-13
Net Weight	0.40 lb(US) (0.181 kg)
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	120 V
Light Source Colour	Green
Type Of Operator	Spring return
Operator Profile	Flush

### Environment

Standards	EN/IEC 60947-1 CSA C22.2 No 14 JIS C 852 JIS C 4520 EN/IEC 60947-5-1 UL 508 EN/IEC 60947-5-4
Product Certifications	UL 508 NEMA
Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X

# Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901040484
Returnability	No
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.80 in (4.572 cm)
Package 1 Width	2.10 in (5.334 cm)
Package 1 Length	3.60 in (9.144 cm)
Package 1 Weight	6.40 oz (181.437 g)

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov