

Product data sheet

Specifications

SQUARE D



selector switch Ø 30 - 3 positions -
spring return to center -
incandescent

9001SK56J1R

Discontinued on: Oct 11, 2019

Discontinued

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Selector switch
Device Short Name	9001SK
Type Of Operator	To centre spring return
Operator Profile	Red standard knob

Complementary

Bezel Material	Plastic
Mounting Diameter	1.18 in (30 mm)
Net Weight	0.13 lb(US) (0.059 kg)
Shape Of Signaling Unit Head	Round
Operator Position Information	3 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Via integral transformer
Light Source	incandescent
Bulb Base	BA 9s
[Us] Rated Supply Voltage	110...120 V AC 50/60 Hz
Compatibility Code	9001SK

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 4X NEMA 6
Standards	EN/IEC 60947-5-4 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1 JIS C 4520 EN/IEC 60947-1 UL 508
Product Certifications	UL 508 NEMA
Vibration Resistance	7 gn 2...500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27

Ordering and shipping details

Category	21429-9001 SK,SKY
Discount Schedule	CS1
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------