Product data sheet

Specifications





Pilot light, Harmony 9001SK, plastic, polycarbonate, domed, amber, 30mm, 110-120V

9001SKP1A9

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 153.00 USD

Main

Range Of Product	Harmony 9001SK	
Product Or Component Type	Pilot light	
Device Short Name	9001SK	
Lens Type	Domed plastic	
Light Block Supply	Via integral transformer 120 V AC 50/60 Hz 6 V)	

Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Round	
Cap/Operator Or Lens Colour	Amber	
Light Source	incandescent	
Bulb Base	BA 9s	
[Us] Rated Supply Voltage	110120 V AC 50/60 Hz	
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Connections - Terminals	Screw clamp terminals, 1 x 0.222 x 1.5 mm² EN/IEC 60947-1	
[Ith] Conventional Free Air Thermal Current	10 A	
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1	
[Ui] Rated Insulation Voltage	250 V 2)EN/IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1	
Operating Position	Any position	
Cad Overall Width	2.13 in (54 mm)	
Cad Overall Height	2.76 in (70 mm)	
Cad Overall Depth	1.65 in (42 mm)	
Net Weight	eight 0.40 lb(US) (0.181 kg)	
Device Presentation	Complete product	
Lens Type	Domed	
[Us] Rated Supply Voltage	110120 V	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Light Block Supply	Via integral transformer	
Supply Frequency	5060 Hz	
Lens Material	Polycarbonate	
Size	30 mm	
Light Source	Incandescent bulb	

Environment

Electrical Shock Protection Class	Class II IEC 61140	
Protective Treatment	TC	
Ip Degree Of Protection	IP66 IEC 60529	
Nema Degree Of Protection	NEMA 1	
	NEMA 12	
	NEMA 13	
	NEMA 2	
	NEMA 3	
	NEMA 3R	
	NEMA 4	
	NEMA 4X	
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	50 gn IEC 60068-2-27	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Standards	EN/IEC 60947-5-1	
	CSA C22.2 No 14	
	EN/IEC 60947-5-4	
	EN/IEC 60947-1	
	JIS C8201-5-1	
	JIS C 852	
	UL 508	
	JIS C8201-1	
Product Certifications	NEMA	
	UL 508	

Ordering and shipping details

Category	US10CS121429	
Discount Schedule	0CS1	
Gtin	785901041122	
Returnability	Yes	
Country Of Origin MX		

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.89 in (4.8 cm)	
Package 1 Width	2.20 in (5.6 cm)	
Package 1 Length	3.70 in (9.4 cm)	
Package 1 Weight	5.92 oz (167.829 g)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

9001SKP1A9

Dimensions Drawings

Dimensions



 \boldsymbol{e} panel thickness: 1 to 6 mm / 0.04 to 0.24 in.