





Push-to-test pilot light, Harmony 9001SK, plastic, polycarbonate, domed, yellow, 30mm, LED yellow, 120V

9001SKT38LYY9



(!) Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-to-test pilot light
Device Short Name	9001SK
Lens Type	Domed plastic
Light Block Supply	Direct 120 V AC/DC

Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Round	
Cap/Operator Or Lens Colour	Yellow	
Light Source	ource Yellow LED	
Bulb Base	BA 9s	
[Us] Rated Supply Voltage	120 V AC/DC	
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Connections - Terminals Screw clamp terminals, 1 x 0.222 x 1.5 mm² EN/IEC 60947-1		
[th] Conventional Free Air 10 A Thermal Current		
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1	
[Ui] Rated Insulation Voltage	250 V 2)EN/IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1	
Operating Position	Any position	
Operating Mode	Push-to-test	
Cad Overall Width	2.13 in (54 mm)	
Cad Overall Height	2.76 in (70 mm)	
Cad Overall Depth	1.65 in (42 mm)	
Net Weight	0.40 lb(US) (0.181 kg)	
Lens Type	Domed	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

[Us] Rated Supply Voltage	120 V	
Light Source Colour	Yellow	
Contacts Type And Composition	1 C/O	
Lens Material	Polycarbonate	
Size	30 mm	
Light Source	LED	

Environment

Electrical Shock Protection Class	Class II IEC 61140
Protective Treatment	тс
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 4X
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Standards	CSA C22.2 No 14
	EN/IEC 60947-5-4
	JIS C 852
	EN/IEC 60947-1
	JIS C8201-5-1
	EN/IEC 60947-5-1
	UL 508
	JIS C8201-1
Product Certifications	UL 508
	NEMA

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901792871
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.08 in (12.903 cm)	
Package 1 Width	2.00 in (5.08 cm)	
Package 1 Length	12.90 in (32.774 cm)	
Package 1 Weight	8.00 oz (226.796 g)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov