Product data sheet

Specifications





Push button, Harmony 9001SK, plastic, flush, green, 30mm, spring return, 1 C/O

9001SKR1GH13

Product availability: Stock - Normally stocked in distribution facility

Price*: 81.00 USD

Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Push-button
Device Short Name	9001SK
Type Of Operator	spring return
Operator Profile	Green flush, unmarked
Operator Additional Information	Plastic guard

Complementary

Bezel Material	Plastic	
Mounting Diameter	1.18 in (30 mm)	
Shape Of Signaling Unit Head	Octagonal	
Contacts Type And Composition	1 C/O	
Contact Operation	Standard	
Connections - Terminals	Screw clamp terminals 1 x 0.222 x 1.5 mm² EN/IEC 60947-1	
Tightening Torque	7.08 lbf.in (0.8 N.m) EN/IEC 60947-1	
Shape Of Screw Head	Cross slotted	
Mechanical Durability	5000000 cycles	
Operating Position	Any position	
[le] Rated Operational Current	3 A 240 V, AC-15, A600-Q600 0.55 A 125 V, DC-13, A600-Q600	
[Ui] Rated Insulation Voltage	250 V 3)EN/IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	2.5 kV EN/IEC 60947-1	
Contacts Material	Silver alloy contacts	
Positive Opening	Without	
Short-Circuit Protection	10 A cartridge fuse EN/IEC 60947-5-1	
[Ith] Conventional Free Air Thermal Current	10 A	
[Icm] Rated Short-Circuit Making Capacity	12 kA 600 V AC-15, 7200 VA 15 kA 480 V AC-15, 7200 VA 30 kA 240 V AC-15, 7200 VA 60 kA 120 V AC-15, 7200 VA 0.1 kA 600 V DC-13 0.27 kA 250 V DC-13 0.55 kA 125 V DC-13	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Rated Breaking Capacity	3 kA 240 V AC-15, 720 VA	
	6 kA 120 V AC-15, 720 VA	
	1.2 kA 600 V AC-15, 720 VA	
	1.5 kA 480 V AC-15, 720 VA	
	0.1 kA 600 V DC-13	
	0.27 kA 250 V DC-13	
	0.55 kA 125 V DC-13	
Net Weight	0.19 lb(US) (0.086 kg)	
Device Presentation	Complete product	
Cap/Operator Or Lens Colour	Green	
Operator Profile	Flush	
Type Of Operator	Spring return	
Size	30 mm	

Environment

Standards	JIS C 4520 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-5-1 UL 508 EN/IEC 60947-1 EN/IEC 60947-5-4
Product Certifications	NEMA UL 508
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Vibration Resistance	7 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	50 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3 NEMA 3R NEMA 4 NEMA 4

Ordering and shipping details

Category	US10CS121429
Discount Schedule	0CS1
Gtin	785901849797
Returnability	Yes
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.01 in (5.1 cm)

Package 1 Width	2.28 in (5.8 cm)	
Package 1 Length	3.70 in (9.4 cm)	
Package 1 Weight	3.21 oz (91.0 g)	

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
Ø	Mercury Free	
9	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

May 13, 2024

Dimensions Drawings

Dimensions




e panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

9001SKR1GH13

Mounting and Clearance

Contact Block Mounting Position

Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2