

# 9012GGW4G21H11V1

pressure switch 9012G - adjustable scale - 2 thresholds - 0 to 175 psig



Price\* : 846.00 USD



9012GGW4G21H11V1 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

## Main

|                                   |   |
|-----------------------------------|---|
| Range of product                  | 9012G   |
| Pressure sensor type              | Electromechanical pressure switch   |
| Pressure sensor name              | 9012G   |
| Pressure sensor size              | 175 psi   |
| Maximum pressure                  | 240 psi   |
| Contacts type and composition     | NC-NO, SPDT-DB, Form Z, snap action, silver nickel contacts                       |
| Controlled fluid                  | Air<br>Hydraulic oil (-40...250 °F)<br>Non-corrosive liquids<br>Non-corrosive gas |
| Fluid connection type             | 0.25 inch 18 NPTF conforming to UL 508  |
| Pressure switch type of operation | Monitors the difference between 2 thresholds                                      |
| Scale type                        | Adjustable differential   |
| Local display                     | With range scale window   |

## Complementary

|   |   |
|---|---|
| Range on decreasing pressure                | 0...175 psi   |
| Approx adjustable differential at mid range | 5...15 psi increasing<br>0.5...36 psi decreasing +/- 2.5 % full scale |
| Terminal block type                         | 4 screw terminals   |
| Electrical connection                       | 1 male connector (mini) 5 pins  |
| Terminal identifier                         | (3)Gnd<br>(1-5)NC<br>(2-4)NO  |
| Electrical circuit type                     | Control circuit   |
| Local signalling                            | 1 LED (clear) DC at 24 V  |
| [In] rated current                          | 2.75 A (Ue = 24 V DC)   |
| Setting                                     | Internal  |
| Enclosure material                          | Die cast aluminium alloy 380  |

|                                 |  |
|---------------------------------|--|
| Pressure actuator               | Diaphragm (nitrile (Buna-N))                                 |
| Height                          | 7.08 in  |
| Depth                           | 2.63 in  |
| Width                           | 3.5 in   |
| Operating position              | Any position   |
| Materials in contact with fluid | Zinc plated steel<br>Nitrile (Buna-N)                        |
| Short-circuit protection        | 10 A by gL (cartridge) overload and short-circuit protection |
| Operating rate                  | <= 120 cyc/mn  |
| Mechanical durability           | 5000000 cycles   |
| Repeat accuracy                 | 4 %  |
| Product weight                  | 3 lb(US)   |

## Environment

|                                       |  |
|---------------------------------------|--|
| Vibration resistance                  | 2 gn conforming to IEC 68-2-6 (f = 40...150 Hz)                                |
| Shock resistance                      | 50 gn conforming to IEC 58-2-27  |
| Standards                             | CE<br>UL 508<br>CSA C22.2 No 14  |
| Product certifications                | CE<br>CSA LR25490 class 3211 03<br>UL listed file E12158 CCN NKPZ and CCN NTHT |
| NEMA degree of protection             | NEMA 4/4X/13 conforming to UL 50   |
| Ambient air temperature for operation | -10...185 °F   |

## Ordering and shipping details

|                       |   |
|-----------------------|---|
| Category              | 21522 - 9012 G INDUSTRIAL PRESSURE SWITCHES |
| Discount Schedule     | CP7G  |
| Nbr. of units in pkg. | 1   |
| Package weight(Lbs)   | 3   |
| Returnability         | N   |
| Country of origin     | MX  |

## Offer Sustainability

|                                  |  |
|----------------------------------|--|
| RoHS (date code: YYWW)           | Will not be compliant<br><b>Will not be compliant</b>  |
| REACH                            | Reference not containing SVHC above the threshold<br><b>Reference not containing SVHC above the threshold</b>              |
| Product environmental profile    | Available  |
| Product end of life instructions | Available  |
| California proposition 65        | WARNING: This product can expose you to chemicals including:   |
| ----- Substance 1                | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                |
| ----- Substance 2                | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information           | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|