



Price\* : 364.00 USD



ⓘ Discontinued

9007TUC2 has not been replaced. Please contact your customer care center for more information.

### Main

Device application	Heavy duty Standard mill switch Universal mill switch
Device short name	T
Series name	Severe duty

### Complementary

[Ith] conventional free air thermal current	20 A
[Ui] rated insulation voltage	600 V
Base plate style	Style C
Body material	Cast zinc
Contact code designation	P600 A600
Contacts material	Silver flashed copper
Contact operation	Snap action
Maximum displacement angle	88 °
Positive opening	Without
Switch actuation	CW
Torque value	12 lbf.in
Tripping angle	5 ° 9 ° initial 16 ° final

### Environment

Ambient air temperature for operation	-10...185 °F
Electrical shock protection class	Class 0
IP degree of protection	IP65 IP66 IP67

NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CSA UL listed CE
Protective treatment	Corrosion resistant gray paint
Shock resistance	30 gn
Standards	UL 508

### Ordering and shipping details

Category	21497 - 9007 FT,T OILTIGHT AND FOUNDRY
Discount Schedule	DS1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------