





Timer, Harmony 9050 JCK, multifunction, programmable, 0.5 second to 999 hours, 10A, 240V AC, 24V AC/DC

9050JCK70V14

Product availability: Stock - Normally stocked in distribution facility

Price*: 173.00 USD

Main

Product Range 9050JCK	
Product Type	Timer
Timing Mode	Watchdog On-delay and off-delay One shot falling edge One shot Trigger on-delay
	Off-delay On-delay Interval Repeat cycle
Timing Range	0.199.9 h 0.059.99 s 0.199.9 min 1999 h 1999 s 1999 min
Supply Voltage	24 V AC

Complementary

· · · · · · · · · · · · · · · · · ·	
Power Consumption	3 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	11
Shape Of Pins	Tubular
For Use With	8501NR62 8501NR61

Environment

Certifications	UL Recognized CE UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Height	2.36 in (60 mm)	
Width	1.73 in (44 mm)	
Depth	3.58 in (91 mm)	

Ordering and shipping details

Category	US10CP221652	
Discount Schedule	0CP2	
Gtin	785901053897	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.90 in (4.826 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	4.48 oz (127.006 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Dimensions Drawings

Approximate Dimensions



Connections and Schema

Connections and Wiring Diagrams



(1) Do not apply DC voltage to the 240 Vac timers (voltage code V24).