

Product data sheet

Specifications

SQUARE D



Terminal Block Assembly, Pressure Wire Clamp, Natural Color, 600VAC/DC 40AMP

9080GP640M

Price*: 147.00 USD

! Discontinued

Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

Complementary

Voltage Rating	600 V AC/DC
Current Rating	40 A UL 40 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 1 marker 40 terminal blocks
Wire Size	AWG 18...AWG 12 copper
Mounting Type	9080GH track
Certifications	CE CSA file 62144 class 6228 01 UL recognized E60616 CCN XCFR2
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Clamp terminal zinc plated steel 18...20 lbf.in (2.03...2.26 N.m) : AWG 18...AWG 10 copper)
Height	1.48 in (37.59 mm)
Width	1.8 in (45.72 mm)
Depth	17 in (431.80 mm)

Ordering and shipping details

Discount Schedule	CP5
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
