

Product data sheet

Specifications



sub-base for plug-in relay ABE7 - 16 channels - relay 10 mm

ABE7P16T212

! Discontinued

Main

| | |
|---------------------------|--|
| Range Of Product | Modicon ABE7 |
| Product Or Component Type | Sub-base for plug-in relay |
| Sub-Base Type | Output sub-base |
| [Us] Rated Supply Voltage | 19...30 V IEC 61131-2 |
| Number Of Channels | 16 |
| Connections - Terminals | Screw type terminals, 1 x 0.09...1 x 1.5 mm ² AWG 28...AWG 16) flexible with cable end Screw type terminals, 1 x 0.14...1 x 2.5 mm ² AWG 26...AWG 12) solid Screw type terminals, 1 x 0.14...1 x 2.5 mm ² AWG 26...AWG 14) flexible without cable end Screw type terminals, 2 x 0.09...2 x 0.75 mm ² AWG 28...AWG 20) flexible with cable end Screw type terminals, 2 x 0.2...2 x 2.5 mm ² AWG 24...AWG 14) solid |

Complementary

| | |
|--|--|
| Supply Voltage Type | DC |
| Product Compatibility | ABS7SC2. ABS7SA2. ABE7ACC20 ABR7S2. |
| Status Led | 1 LED per channel (Green) channel status 1 LED (Green) power ON |
| Polarity Distribution | Polarity distribution contact common per 2 groups of 8 channels |
| Short-Circuit Protection | 1 A internal fuse, 5 x 20 mm, fast blow PLC end) |
| Fixing Mode | By clips (35 mm symmetrical DIN rail) By screws (solid plate with fixing kit) |
| Maximum Supply Current | 1 A |
| Voltage Drop On Power Supply Fuse | 0.3 V |
| Maximum Current Per Output Common | 16 A |
| [Ui] Rated Insulation Voltage | 300 V coil circuit/contact circuits IEC 60947-1 2000 V terminals/mounting rails |
| [Uimp] Rated Impulse Withstand Voltage | 2.5 kV |
| Installation Category | II IEC 60664-1 |
| Tightening Torque | 5.31 lbf.in (0.6 N.m) flat Ø 3.5 mm |
| Net Weight | 1.36 lb(US) (0.615 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|---------------------------------------|--|
| Product Certifications | CSA DNV UL GL |
| Ip Degree Of Protection | IP2X conforming to IEC 60529 |
| Resistance To Incandescent Wire | 1382 °F (750 °C) IEC 60695-2-11 |
| Shock Resistance | 15 gn 11 ms IEC 60068-2-27 |
| Vibration Resistance | 2 gn 10...150 Hz)IEC 60068-2-6 |
| Resistance To Electrostatic Discharge | 4 kV contact) level 3 IEC 61000-4-2 8 kV air) level 3 IEC 61000-4-2 |
| Resistance To Radiated Fields | 9.14 V/m (10 V/m) 26000000...1000000000 Hz)IEC 61000-4-3 level 3 |
| Resistance To Fast Transients | 2 kV level 3 IEC 61000-4-4 |
| Ambient Air Temperature For Operation | 23...140 °F (-5...60 °C) IEC 61131-2 |
| Ambient Air Temperature For Storage | -40...176 °F (-40...80 °C) IEC 61131-2 |
| Pollution Degree | 2 IEC 60664-1 |

Ordering and shipping details

| | |
|-------------------|---------------------------------|
| Category | 22375-INTERFACE MODULE(ABA,R,S) |
| Discount Schedule | CP2 |
| Gtin | 00785901901129 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free


 RoHS Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings


Dimensions



(1) ABE7BV10 / BV20, ABE7BV10E / BV20E


Mounting and Clearance

Mounting




Connections and Schema

HE10 16 Channels




Wiring Diagram



- (1) Inductive load
- (2) Fuse only for ABE7P16T215
- (3) ABR7S21 (1 "F"/SPDT) (not supplied)
- (4) ABS7SC2E (5...48 VDC) I max. = 0.5 A (not supplied)
- (5) ABS7SA2M (24...240 VAC) I max. = 0.5 A (not supplied)

Wiring Diagram with ABE7ACC20




- (1) Inductive load
- (2) Fuse only for ABE7P16T215
- (3) ABR7S21 (1 "F"/SPDT) (not supplied)
- (4) ABS7SC2E (5...48 VDC) I max. = 0.5 A (not supplied)
- (6) ABE7ACC20 (24 VDC) (not supplied/not isolated)

Performance Curves

Curves for Determining Cable Type and Length According to the Current


16-channel Sub-base



- L Cable length
- I_T Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.

Temperature Derating Curves



- (1) 100 % of channels used
- (2) 50 % of channels used