

Product data sheet

Specifications

SQUARE D



Power distribution block, Linergy, 2 pole, 1 line, 6 load, 380A CU, 600 V

9080LBC263106

Discontinued on: Jan 31, 2024

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	9080LB
Product	Power Distribution Block
Current Rating	380 A copper

Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number Of Poles	2
Terminals Per Pole	1 line 6 load
Wire Size	Line 6, AWG 4...500 kcmil, copper Load 1, AWG 14...AWG 2, copper
Electrical Connection	Tin plated copper lugs
Sccr	100 kA UL 508 A
Ambient Air Temperature For Operation	-40...302 °F (-40...150 °C)
Block Material	Phenolic: block
Terminal Tightening Torque	Load lug 40 lbf.in (4.52 N.m) AWG 8 copper Load lug 35 lbf.in (3.95 N.m) AWG 14...AWG 10 copper Line lug 375 lbf.in (42.37 N.m) AWG 4...500 kcmil copper Load lug 50 lbf.in (5.65 N.m) AWG 2 copper Load lug 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper
Wire Stripping Length	Line: 1.06 in (26.92 mm) Load: 1 in (25.40 mm) for bottom connection Load: 1.56 in (39.62 mm) for top connection
Height	4 in (101.60 mm)
Width	3.47 in (88.14 mm)
Depth	2.61 in (66.29 mm)
End Barrier	9080LB32

Environment

Certifications	UL recognized E60616 CCN XCFR2 CE CSA file 70361 class 6228 01
----------------	--

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US10CP121711
Discount Schedule	0CP1
Gtin	785901157113
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	5.20 in (13.208 cm)
Package 1 Weight	27.36 oz (775.643 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	