



Overview

Model Name	Rack PDU, Basic, Half Height, 200-208V, 30A, (14) C13, (2) C19
Includes	Installation guide , Safety guide
Standard Lead Time	Usually in Stock
Product Distribution	Canada , United States

Output

Nominal Output Voltage	200V , 208V
Maximum Total Current Draw per Phase	30 A
Output Connections	(14) IEC 320 C13 (Battery Backup) , (2) IEC 320 C19 (Battery Backup)
Overload Protection	Yes

Input

Nominal Input Voltage	208V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	24 A
Input Connections	NEMA L6-30P
Cord Length	10 feet (3.05 meters)
Acceptable Input Voltage	200-240 VAC
Maximum Line Current per phase	30 A
Maximum Input Current per phase	30 A

Physical

Net Weight	6.12 lbs (2.78 kg)
Maximum Height	32.81 inches (833.0 mm)
Maximum Width	2.21 inches (56.0 mm)
Maximum Depth	1.85 inches (47.0 mm)
Shipping Weight	7.13 lbs (3.24 kg)
Shipping Height	38.03 inches (966.0 mm)
Shipping Width	6.14 inches (156.0 mm)

Shipping Depth	5.4 inches (137.0 mm)
Color	Black

Environmental

Operating Environment	32 - 122 °F (0 - 50 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 149 °F (-15 - 65 °C)
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	UL Listed , cUL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs