



Overview

Model Name	Rack PDU, Basic, Zero U, 14.4kW, 208 V, (6) C19 & (3) C13, High Temp
Includes	Cord retention bracket(s) , Installation guide , Rack Mounting brackets , Toolless Mounting Kit
Standard Lead Time	Usually in Stock
Product Distribution	Aruba , Barbados , Bermuda , Canada , Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guatemala , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Taiwan , Trinidad And Tobago , United States , Venezuela

Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	40 A
Output Connections	(3) IEC 320 C13 (Battery Backup) , (6) IEC 320 C19 (Battery Backup)
Overload Protection	Yes

Input

Nominal Input Voltage	208 3PH
Input Frequency	47 - 63 Hz
Regulatory Derated Input Current (North America)	40 A
Input Connections	CS8365
Cord Length	6 feet (1.83 meters)
Number of Power Cords	1
Maximum Line Current per phase	40 A
Maximum Input Current per phase	50 A

Physical

Net Weight	15.96 lbs (7.26 kg)
Maximum Height	36.5 inches (927.0 mm)
Maximum Width	2.16 inches (55.0 mm)
Maximum Depth	3.46 inches (88.0 mm)
Shipping Weight	19.27 lbs (8.76 kg)
Shipping Height	42.0 inches (1067.0 mm)

Shipping Width	11.76 inches (298.0 mm)
Shipping Depth	3.26 inches (83.0 mm)
Color	Black

Environmental

Operating Environment	23 - 140 °F (-5 - 60 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA C22.2 No. 60950-1-03 , METI Denan , UL 60950-1 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------