



Overview

Description	APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
Model Name	Rack PDU 2G, Switched, ZeroU, 15A, 100-120V, (8) 5-15
Includes	Installation guide , Rack Mounting brackets , Safety guide , Serial configuration cable
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Japan , United States

Output

Nominal Output Voltage	100V , 120V
Output Connections	(8) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	100V 120V
Input Frequency	50/60 Hz
Regulatory Derated Input Current (North America)	12 A
Input Connections	NEMA 5-15P
Cord Length	10 feet (3.05 meters)
Number of Power Cords	1
Acceptable Input Voltage	100-120 VAC
Maximum Input Current per phase	15 A
Load Capacity	1440 VA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Physical

Net Weight	9.15 lbs (4.16 kg)
Maximum Height	38.9 inches (988.0 mm)
Maximum Width	2.19 inches (55.0 mm)
Maximum Depth	1.82 inches (46.0 mm)
Shipping Weight	11.04 lbs (5.02 kg)
Shipping Height	44.53 inches (1131.0 mm)
Shipping Width	6.3 inches (160.0 mm)
Shipping Depth	4.26 inches (109.0 mm)
Color	Black

Environmental

Operating Environment	23 - 113 °F (-5 - 45 °C)
Operating Relative Humidity	5 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-13 - 149 °F (-25 - 65 °C)
Storage Relative Humidity	5 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	FCC Part 15 Class A , ICES-003 , PSE , UL 60950-1 , UL Listed , cUL Listed
Standard warranty	2 years repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant