# **Product data sheet**

Specification





servo motor BCH, Lexium 28, 100mm, 2000W, 4.35kg.cm<sup>2</sup>, with oil seal, with key, brake, straight connection

BCH2LH2033CF6C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,675.20 USD

#### Main

Range Compatibility	Lexium 28	
Product Or Component Type	Servo motor	
Device Short Name	BCH2	

## Complementary

Maximum Mechanical Speed	5000 rpm
[Us] Rated Supply Voltage	220 V
Phase	Three phase
Continuous Stall Current	9.87 A
Continuous Stall Torque	56.38 lbf.in (6.37 N.m) LXM26D 12 A, 220 V, three phase 56.38 lbf.in (6.37 N.m) LXM28 12 A, 220 V, three phase
Continuous Power	2000 W
Peak Stall Torque	169.14 lbf.in (19.11 N.m) LXM26D 12 A, 220 V, three phase 169.14 lbf.in (19.11 N.m) LXM28 12 A, 220 V, three phase
Nominal Output Power	2000 W LXM26D 12 A, 220 V, three phase 2000 W LXM28 12 A, 220 V, three phase
Nominal Torque	56.38 lbf.in (6.37 N.m) LXM26D 12 A, 220 V, three phase 56.38 lbf.in (6.37 N.m) LXM28 12 A, 220 V, three phase
Nominal Speed	3000 rpm LXM26D 12 A, 220 V, three phase 3000 rpm LXM28 12 A, 220 V, three phase
Maximum Current Irms	32.3 A LXM26D 2 kW, 220 V 32.3 A LXM28 2 kW, 220 V
Maximum Permanent Current	10.27 A
Product Compatibility	LXM26D servo drive 2 kW, 220 V, three phase LXM28 servo drive 2 kW, 220 V, three phase
Shaft End	Keyed
Shaft Diameter	0.87 in (22 mm)
Shaft Length	1.77 in (45 mm)
Key Width	0.31 in (8 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	57.53 lbf.in (6.5 N.m) built-in

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mounting Support	Asian standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Connector MIL
Torque Constant	0.65 N.m/A 68 °F (20 °C)
Back Emf Constant	39 V/krpm 68 °F (20 °C)
Rotor Inertia	4.35 kg.cm²
Stator Resistance	0.36 Ohm 68 °F (20 °C)
Stator Inductance	2.59 mH 68 °F (20 °C)
Stator Electrical Time Constant	7.19 ms 68 °F (20 °C)
Maximum Radial Force Fr	570 N 3000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	10.4 W
Type Of Cooling	Natural convection
Length	8.88 in (225.5 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.28 in (7 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Distance Shaft Shoulder-Flange	0.28 in (7 mm)
Net Weight	15.87 lb(US) (7.2 kg)

### **Environment**

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

## Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480734113
Returnability	No
Country Of Origin	CN

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.1 cm)
Package 1 Width	9.06 in (23 cm)
Package 1 Length	14.17 in (36 cm)
Package 1 Weight	20.35 lb(US) (9.23 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	


### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

#### **Dimensions Drawings**

#### **Dimensions**

#### **Dimensions of Motor**



	mm	in.
L (without holding brake)	198.5	7.81
L (with holding brake)	225.5	8.88
Z	141	5.55

#### Performance Curves

#### Torque/Speed Curves with 230 V Three Phase Supply Voltage

## Servo Motor with LXM28AU20●●● Servo Drive

1000

M [Nm]

20

Mmax

16

12

8

M0

2

4

2000

3000

4000

5000 n [min<sup>-1</sup>]

1: Peak torque

0

2: Continuous torque