Product data sheet

Specifications





() Discontinued

servo motor BCH, Lexium 28, 130mm, 1000W, 6.63kg.cm², without oil seal, with key, straight connection

BCH2MM1021CA6C

Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

molomontary

Complementary	
Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V
Phase	Three phase Single phase
Continuous Stall Current	5.77 A
Continuous Stall Torque	42.22 lbf.in (4.77 N.m) LXM28 7 A, 220 V, single phase 42.22 lbf.in (4.77 N.m) LXM28 7 A, 220 V, three phase
Continuous Power	1000 W
Peak Stall Torque	126.57 lbf.in (14.3 N.m) LXM28 7 A, 220 V, single phase 126.57 lbf.in (14.3 N.m) LXM28 7 A, 220 V, three phase
Nominal Output Power	1000 W LXM28 7 A, 220 V, single phase 1000 W LXM28 7 A, 220 V, three phase
Nominal Torque	42.22 lbf.in (4.77 N.m) LXM28 7 A, 220 V, single phase 42.22 lbf.in (4.77 N.m) LXM28 7 A, 220 V, three phase
Nominal Speed	2000 rpm LXM28 7 A, 220 V, single phase 2000 rpm LXM28 7 A, 220 V, three phase
Maximum Current Irms	19.64 A LXM28 1 kW, 220 V
Maximum Permanent Current	6.29 A
Product Compatibility	LXM28 servo drive 1 kW, 220 V, single phase LXM28 servo drive 1 kW, 220 V, three phase
Shaft End	Keyed
Shaft Diameter	0.87 in (22 mm)
Shaft Length	2.17 in (55 mm)
Key Width	0.31 in (8 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	Without
Mounting Support	Asian standard flange

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Motor Flange Size	5.12 in (130 mm)
Electrical Connection	Connector MIL
Torque Constant	0.83 N.m/A 68 °F (20 °C)
Back Emf Constant	50 V/krpm 68 °F (20 °C)
Rotor Inertia	6.63 kg.cm ²
Stator Resistance	0.62 Ohm 68 °F (20 °C)
Stator Inductance	7.4 mH 68 °F (20 °C)
Stator Electrical Time Constant	11.94 ms 68 °F (20 °C)
Maximum Radial Force Fr	670 N 2000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	5.79 in (147 mm)
Number Of Motor Stacks	1
Centring Collar Diameter	4.33 in (110 mm)
Centring Collar Depth	0.31 in (8 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	5.71 in (145 mm)
Distance Shaft Shoulder-Flange	0.31 in (8 mm)
Net Weight	15.43 lb(US) (7 kg)

Environment

Ip Degree Of Protection	IP54 IM B5, IM V1 IP50 IM V3
Ambient Air Temperature For Operation	-4104 °F (-2040 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480734229
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.1 cm)
Package 1 Width	9.06 in (23.0 cm)
Package 1 Length	14.17 in (36.0 cm)
Package 1 Weight	17.79 lb(US) (8.07 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	147	5.79
L (with holding brake)	183	7.2
Z	94.5	3.72

Product data sheet BCH2MM1021CA6C

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage



Servo Motor with LXM28AU10 ••• Servo Drive

- 1: Peak torque
- 2: Continuous torque