Product data sheet

Specification





servo motor BCH, Lexium 28, 80mm, 750W, with oil seal, smooth, leads connection

BCH2HF0732CA5C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,571.53 USD

Main

Range Compatibility	Lexium 28	
Product Or Component Type	Servo motor	
Device Short Name	BCH2	

Complementary

Maximum Mechanical Speed	5000 rpm
[Us] Rated Supply Voltage	220 V 110 V
Phase	Three phase Single phase
Continuous Stall Current	4.01 A
Continuous Stall Torque	21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase
Continuous Power	750 W
Peak Stall Torque	63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, single phase 63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, three phase 63.37 lbf.in (7.16 N.m) LXM28 9 A, 110 V, single phase
Nominal Output Power	750 W LXM28 4.5 A, 220 V, single phase 750 W LXM28 4.5 A, 220 V, three phase 750 W LXM28 9 A, 110 V, single phase
Nominal Torque	21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase
Nominal Speed	3000 rpm LXM28 4.5 A, 220 V, single phase 3000 rpm LXM28 4.5 A, 220 V, three phase 3000 rpm LXM28 9 A, 110 V, single phase
Maximum Current Irms	13.23 A LXM28 0.75 kW, 220 V 13.23 A LXM28 0.75 kW, 110 V
Maximum Permanent Current	4.29 A
Product Compatibility	LXM28 servo drive 0.75 kW, 220 V, single phase LXM28 servo drive 0.75 kW, 220 V, three phase LXM28 servo drive 0.75 kW, 110 V, single phase
Shaft End	Smooth shaft
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.38 in (35 mm)
Feedback Type	20 bits single turn absolute encoder

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Holding Brake	Without
Mounting Support	Asian standard flange
Motor Flange Size	3.15 in (80 mm)
Electrical Connection	Free lead
Torque Constant	0.6 N.m/A 68 °F (20 °C)
Back Emf Constant	36 V/krpm 68 °F (20 °C)
Rotor Inertia	1.54 kg.cm²
Stator Resistance	1.5 Ohm 68 °F (20 °C)
Stator Inductance	6.1 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.07 ms 68 °F (20 °C)
Maximum Radial Force Fr	332 N 3000 rpm
Maximum Axial Force Fa	115 N
Brake Pull-In Power	10.2 W
Type Of Cooling	Natural convection
Length	5.43 in (138 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	2.76 in (70 mm)
Centring Collar Depth	0.16 in (4 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.26 in (6.6 mm)
Circle Diameter Of The Mounting Holes	3.54 in (90 mm)
Distance Shaft Shoulder-Flange	0.16 in (4 mm)
Net Weight	6.39 lb(US) (2.9 kg)

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1	
Ambient Air Temperature For Operation	-4104 °F (-2040 °C)	

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480733765
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.43 in (13.8 cm)
Package 1 Width	6.89 in (17.5 cm)
Package 1 Length	11.65 in (29.6 cm)

Package 1 Weight	7.66 lb(US) (3.475 kg)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	2	
Package 2 Height	11.81 in (30.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight	16.62 lb(US) (7.54 kg)	

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Mercury Free	
	Rohs Exemption Information	Yes
②	Pvc Free	


Certifications & Standards

Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope)	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	138	5.43
L (with holding brake)	178	7.01
A	35	1.38
С	29.5	1.16
D	19	0.75
F	25	0.98
R	15.5	0.61
Т	6	0.24
V	6	0.24
W	6	0.24
Z	93	3.66

BCH2HF0732CA5C

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with LXM28AU04●●● Servo Drive M [Nm]



- 1: Peak torque
- 2: Continuous torque