

Product data sheet

Specifications



servo motor BCH, Lexium 28,
130mm, 2000W, without oil seal,
with key, brake, straight
connection

BCH2MM2021CF6C

! Discontinued

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range Compatibility	Lexium 28
Device Short Name	BCH2
Product Or Component Type	Servo motor

Complementary

Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V
Phase	Three phase
Continuous Stall Current	9.95 A
Continuous Stall Torque	84.52 lbf.in (9.55 N.m) LXM28... 12 A, 220 V, three phase
Continuous Power	2000 W
Peak Stall Torque	253.57 lbf.in (28.65 N.m) LXM28... 12 A, 220 V, three phase
Nominal Output Power	2000 W LXM28... 12 A, 220 V, three phase
Nominal Torque	84.52 lbf.in (9.55 N.m) LXM28... 12 A, 220 V, three phase
Nominal Speed	2000 rpm LXM28... 12 A, 220 V, three phase
Maximum Current Irms	32.85 A LXM28... 2 kW, 220 V
Maximum Permanent Current	11.25 A
Product Compatibility	LXM28... servo drive 2 kW, 220 V, three phase
Shaft End	Keyed
Shaft Diameter	0.87 in (22 mm)
Shaft Length	2.17 in (55 mm)
Key Width	0.31 in (8 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	84.97 lbf.in (9.6 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	5.12 in (130 mm)
Electrical Connection	Connector MIL

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Torque Constant	0.96 N.m/A 68 °F (20 °C)
Back Emf Constant	58 V/krpm 68 °F (20 °C)
Rotor Inertia	14.1 kg.cm²
Stator Resistance	0.34 Ohm 68 °F (20 °C)
Stator Inductance	4.5 mH 68 °F (20 °C)
Stator Electrical Time Constant	13.24 ms 68 °F (20 °C)
Maximum Radial Force Fr	670 N 2000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	8.50 in (216 mm)
Number Of Motor Stacks	4
Centring Collar Diameter	4.33 in (110 mm)
Centring Collar Depth	0.31 in (8 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	5.71 in (145 mm)
Distance Shaft Shoulder-Flange	0.31 in (8 mm)
Net Weight	24.25 lb(US) (11 kg)

Environment

Ip Degree Of Protection	IP54 IM B5, IM V1 IP50 IM V3
Ambient Air Temperature For Operation	32...104 °F (0...40 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480734397
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.1 cm)
Package 1 Width	9.06 in (23.0 cm)
Package 1 Length	14.17 in (36.0 cm)
Package 1 Weight	22.51 lb(US) (10.21 kg)

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	187	7.36
L (with holding brake)	216	8.5
Z	134.5	5.30

Performance Curves

Torque/Speed Curves with 230 V Three Phase Supply Voltage

Servo Motor with LXM28AU20 Servo Drive



- 1 : Peak torque
- 2 : Continuous torque