Product data sheet

Specifications





servo motor BCH, Lexium 28, 80mm, 750W, 1.59kg.cm², with oil seal, with key, brake, leads connection

BCH2HF0733CF5C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 954.92 USD

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary

Maximum Mechanical Speed	5000 rpm	
[Us] Rated Supply Voltage	220 V 110 V	
Phase	Single phase Three phase	
Continuous Stall Current	4.01 A	
Continuous Stall Torque	21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase	
Continuous Power	750 W	
Peak Stall Torque	63.37 lbf.in (7.16 N.m) LXM26D 4.5 A, 220 V, single phase 63.37 lbf.in (7.16 N.m) LXM26D 4.5 A, 220 V, three phase 63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, single phase 63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, three phase 63.37 lbf.in (7.16 N.m) LXM28 9 A, 110 V, single phase	
Nominal Output Power	750 W LXM26D 4.5 A, 220 V, single phase 750 W LXM26D 4.5 A, 220 V, three phase 750 W LXM28 4.5 A, 220 V, single phase 750 W LXM28 4.5 A, 220 V, three phase 750 W LXM28 9 A, 110 V, single phase	
Nominal Torque	21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase	
Nominal Speed	3000 rpm LXM26D 4.5 A, 220 V, single phase 3000 rpm LXM26D 4.5 A, 220 V, three phase 3000 rpm LXM28 4.5 A, 220 V, single phase 3000 rpm LXM28 4.5 A, 220 V, three phase 3000 rpm LXM28 9 A, 110 V, single phase	
Maximum Current Irms	13.23 A LXM28 0.75 kW, 220 V 13.23 A LXM28 0.75 kW, 110 V	
Maximum Permanent Current	4.29 A	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Compatibility	LXM26D servo drive 0.75 kW, 220 V, single phase LXM26D servo drive 0.75 kW, 220 V, three phase LXM28 servo drive 0.75 kW, 220 V, single phase LXM28 servo drive 0.75 kW, 220 V, three phase LXM28 servo drive 0.75 kW, 110 V, single phase
Shaft End	Keyed
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.38 in (35 mm)
Key Width	0.24 in (6 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	22.13 lbf.in (2.5 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	3.15 in (80 mm)
Electrical Connection	Free lead
Torque Constant	0.6 N.m/A 68 °F (20 °C)
Back Emf Constant	36 V/krpm 68 °F (20 °C)
Rotor Inertia	1.59 kg.cm ²
Stator Resistance	1.5 Ohm 68 °F (20 °C)
Stator Inductance	6.1 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.07 ms 68 °F (20 °C)
Maximum Radial Force Fr	332 N 3000 rpm
Maximum Axial Force Fa	115 N
Brake Pull-In Power	10.2 W
Type Of Cooling	Natural convection
Length	7.01 in (178 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	2.76 in (70 mm)
Centring Collar Depth	0.16 in (4 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.26 in (6.6 mm)
Circle Diameter Of The Mounting Holes	3.54 in (90 mm)
Distance Shaft Shoulder-Flange	0.16 in (4 mm)
Net Weight	8.16 lb(US) (3.7 kg)

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53

Gtin	3606480733796
Returnability	No
Country Of Origin	CN

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.67 in (14.4 cm)
Package 1 Width	7.01 in (17.8 cm)
Package 1 Length	12.05 in (30.6 cm)
Package 1 Weight	9.44 lb(US) (4.28 kg)
Unit Type Of Package 2	S06
Number Of Units In Package 2	24
Package 2 Height	28.94 in (73.5 cm)
Package 2 Width	23.62 in (60.0 cm)
Package 2 Length	31.50 in (80.0 cm)
Package 2 Weight	249.12 lb(US) (113.0 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards


REACh Declaration	
Pro-active compliance (Product out of EU RoHS legal scope)	
China RoHS declaration	
Product Environmental Profile	
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
End of Life Information	
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	


Product data sheet

Dimensions Drawings

Dimensions

Dimensions of Motor






	mm	in.
L (without holding brake)	138	5.43
L (with holding brake)	178	7.01
A	35	1.38
с	29.5	1.16
D	19	0.75
F	25	0.98
R	15.5	0.61
Т	6	0.24
V	6	0.24
w	6	0.24
Z	93	3.66

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage



Servo Motor with LXM28AU04 ••• Servo Drive

- 1: Peak torque
- 2: Continuous torque