# **Product data sheet**

Specifications





servo motor BCH, Lexium 28, 60mm, 200W, 0.17kg.cm², without oil seal, smooth, brake, leads connection

BCH2LD0230CF5C



! Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

### Complementary

Maximum Mechanical Speed	5000 rpm
[Us] Rated Supply Voltage	220 V 110 V
Phase	Single phase Three phase
Continuous Stall Current	1.11 A
Continuous Stall Torque	5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 3.6 A, 110 V, single phase
Continuous Power	200 W
Peak Stall Torque	16.99 lbf.in (1.92 N.m) LXM28 1.5 A, 220 V, single phase 16.99 lbf.in (1.92 N.m) LXM28 1.5 A, 220 V, three phase 16.99 lbf.in (1.92 N.m) LXM28 3.6 A, 110 V, single phase
Nominal Output Power	200 W LXM28 1.5 A, 220 V, single phase 200 W LXM28 1.5 A, 220 V, three phase 200 W LXM28 3.6 A, 110 V, single phase
Nominal Torque	5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, single phase 5.66 lbf.in (0.64 N.m) LXM28 1.5 A, 220 V, three phase 5.66 lbf.in (0.64 N.m) LXM28 3.6 A, 110 V, single phase
Nominal Speed	3000 rpm LXM28 1.5 A, 220 V, single phase 3000 rpm LXM28 1.5 A, 220 V, three phase 3000 rpm LXM28 3.6 A, 110 V, single phase
Maximum Current Irms	4.31 A LXM28 0.2 kW, 220 V 4.31 A LXM28 0.2 kW, 110 V
Maximum Permanent Current	1.3 A
Product Compatibility	LXM28 servo drive 0.2 kW, 220 V, single phase LXM28 servo drive 0.2 kW, 220 V, three phase LXM28 servo drive 0.2 kW, 110 V, single phase
Shaft End	Smooth shaft
Shaft Diameter	0.55 in (14 mm)
Shaft Length	1.18 in (30 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	11.51 lbf.in (1.3 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	2.36 in (60 mm)
Electrical Connection	Free lead
Torque Constant	0.58 N.m/A 68 °F (20 °C)
Back Emf Constant	35 V/krpm 68 °F (20 °C)
Rotor Inertia	0.17 kg.cm <sup>2</sup>
Stator Resistance	12.2 Ohm 68 °F (20 °C)
Stator Inductance	22.5 mH 68 °F (20 °C)
Stator Electrical Time Constant	1.84 ms 68 °F (20 °C)
Maximum Radial Force Fr	200 N 3000 rpm
Maximum Axial Force Fa	70 N
Brake Pull-In Power	11.2 W
Type Of Cooling	Natural convection
Length	5.51 in (140 mm)
Number Of Motor Stacks	1
Centring Collar Diameter	1.97 in (50 mm)
Centring Collar Depth	0.22 in (5.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	2.76 in (70 mm)
Distance Shaft Shoulder-Flange	0.22 in (5.5 mm)
Net Weight	3.31 lb(US) (1.5 kg)

### **Environment**

Ip Degree Of Protection	IP54 IM B5, IM V1 IP50 IM V3
Ambient Air Temperature For	32104 °F (040 °C)

## Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480733499
Returnability	No
Country Of Origin	CN

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.37 in (11.1 cm)

Package 1 Width	5.71 in (14.5 cm)
Package 1 Length	10.43 in (26.5 cm)
Package 1 Weight	4.59 lb(US) (2.08 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>②</b>	Mercury Free	
<b>②</b>	Rohs Exemption Information Yes	
<b>⊘</b>	Pvc Free	


#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
<b>Environmental Disclosure</b>	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

#### **Dimensions Drawings**

#### **Dimensions**

#### **Dimensions of Motor**




	mm	in.
L (without holding brake)	104	4.09
L (with holding brake)	140	5.51
Z	57	2.24

#### Performance Curves

#### Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

### Servo Motor with LXM28AU02●●● Servo Drive



- 1: Peak torque
- 2: Continuous torque