Product data sheet

Specification





servo motor BCH, Lexium 28, 100mm, 1000W, 2.45kg.cm², with oil seal, with key, brake, straight connection

BCH2LH1033CF6C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,336.89 USD

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary

Maximum Mechanical Speed	5000 rpm
[Us] Rated Supply Voltage	220 V
Phase	Single phase Three phase
Continuous Stall Current	5.83 A
Continuous Stall Torque	28.15 lbf.in (3.18 N.m) LXM26D 7 A, 220 V, single phase 28.15 lbf.in (3.18 N.m) LXM26D 7 A, 220 V, three phase 28.15 lbf.in (3.18 N.m) LXM28 7 A, 220 V, single phase 28.15 lbf.in (3.18 N.m) LXM28 7 A, 220 V, three phase
Continuous Power	1000 W
Peak Stall Torque	84.44 lbf.in (9.54 N.m) LXM26D 7 A, 220 V, single phase 84.44 lbf.in (9.54 N.m) LXM26D 7 A, 220 V, three phase 84.44 lbf.in (9.54 N.m) LXM28 7 A, 220 V, single phase 84.44 lbf.in (9.54 N.m) LXM28 7 A, 220 V, three phase
Nominal Output Power	1000 W LXM26D 7 A, 220 V, single phase 1000 W LXM26D 7 A, 220 V, three phase 1000 W LXM28 7 A, 220 V, single phase 1000 W LXM28 7 A, 220 V, three phase
Nominal Torque	28.15 lbf.in (3.18 N.m) LXM26D 7 A, 220 V, single phase 28.15 lbf.in (3.18 N.m) LXM26D 7 A, 220 V, three phase 28.15 lbf.in (3.18 N.m) LXM28 7 A, 220 V, single phase 28.15 lbf.in (3.18 N.m) LXM28 7 A, 220 V, three phase
Nominal Speed	3000 rpm LXM26D 7 A, 220 V, single phase 3000 rpm LXM26D 7 A, 220 V, three phase 3000 rpm LXM28 7 A, 220 V, single phase 3000 rpm LXM28 7 A, 220 V, three phase
Maximum Current Irms	18.9 A LXM28 1 kW, 220 V
Maximum Permanent Current	6.64 A
Product Compatibility	LXM26D servo drive 1 kW, 220 V, single phase LXM26D servo drive 1 kW, 220 V, three phase LXM28 servo drive 1 kW, 220 V, single phase LXM28 servo drive 1 kW, 220 V, three phase
Shaft End	Keyed

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Diameter	0.87 in (22 mm)
Shaft Length	1.77 in (45 mm)
Key Width	0.31 in (8 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	57.53 lbf.in (6.5 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Connector MIL
Torque Constant	0.55 N.m/A 68 °F (20 °C)
Back Emf Constant	33 V/krpm 68 °F (20 °C)
Rotor Inertia	2.45 kg.cm ²
Stator Resistance	0.67 Ohm 68 °F (20 °C)
Stator Inductance	4.2 mH 68 °F (20 °C)
Stator Electrical Time Constant	6.27 ms 68 °F (20 °C)
Maximum Radial Force Fr	570 N 3000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	10.4 W
Type Of Cooling	Natural convection
Length	7.11 in (180.5 mm)
Number Of Motor Stacks	1
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.28 in (7 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Distance Shaft Shoulder-Flange	0.28 in (7 mm)
Net Weight	11.24 lb(US) (5.1 kg)

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480734038
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.09 in (18.0 cm)
Package 1 Width	14.17 in (36.0 cm)
Package 1 Length	10.83 in (27.5 cm)
Package 1 Weight	15.94 lb(US) (7.23 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Mercury Free	
②	Rohs Exemption Information Yes	
⊘	Pvc Free	

Certifications & Standards


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

BCH2LH1033CF6C

Dimensions Drawings

Dimensions

Dimensions of Motor




	mm	in.
L (without holding brake)	153.5	6.04
L (with holding brake)	180.5	7.11
Z	96	3.78

Performance Curves

Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

Servo Motor with LXM28AU10●●● Servo Drive

M [Nm]



1: Peak torque

2: Continuous torque