Product data sheet

Specification





3000 rpm

servo motor BCH, Lexium 28, 180mm, 3000W, with oil seal, smooth, brake, straight connection

BCH2MR3022CF6C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6,114.15 USD

Main

Range Compatibility	Lexium 28
Product Or Component Type	Servo motor
Device Short Name	BCH2

Complementary Maximum Mechanical Speed

maximum meenamear opeca	3000 TpITI
[Us] Rated Supply Voltage	220 V
Phase	Three phase
Continuous Stall Current	16.33 A
Continuous Stall Torque	126.74 lbf.in (14.32 N.m) LXM28 19.8 A, 220 V, three phase
Continuous Power	3000 W
Peak Stall Torque	380.32 lbf.in (42.97 N.m) LXM28 19.8 A, 220 V, three phase
Nominal Output Power	3000 W LXM28 19.8 A, 220 V, three phase
Nominal Torque	126.74 lbf.in (14.32 N.m) LXM28 19.8 A, 220 V, three phase
Nominal Speed	2000 rpm LXM28 19.8 A, 220 V, three phase
Maximum Current Irms	53.9 A LXM28 3 kW, 220 V
Maximum Permanent Current	18.8 A
Product Compatibility	LXM28 servo drive 3 kW, 220 V, three phase
Shaft End	Smooth shaft
Shaft Diameter	1.38 in (35 mm)
Shaft Length	3.11 in (79 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	424.84 lbf.in (48 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	7.09 in (180 mm)
Electrical Connection	Connector MIL
Torque Constant	0.88 N.m/A 68 °F (20 °C)
Back Emf Constant	53 V/krpm 68 °F (20 °C)
Rotor Inertia	54.1 kg.cm²

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Stator Resistance	0.131 Ohm 68 °F (20 °C)
Stator Inductance	2.7 mH 68 °F (20 °C)
Stator Electrical Time Constant	20.61 ms 68 °F (20 °C)
Maximum Radial Force Fr	1200 N 2000 rpm
Maximum Axial Force Fa	497 N
Brake Pull-In Power	49.6 W
Type Of Cooling	Natural convection
Length	9.25 in (235 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	4.50 in (114.3 mm)
Centring Collar Depth	0.16 in (4 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.53 in (13.5 mm)
Circle Diameter Of The Mounting Holes	7.87 in (200 mm)
Distance Shaft Shoulder-Flange	0.16 in (4 mm)
Net Weight	50.71 lb(US) (23 kg)

Environment

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53
Gtin	3606480734816
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.65 in (24.5 cm)
Package 1 Width	11.42 in (29.0 cm)
Package 1 Length	23.03 in (58.5 cm)
Package 1 Weight	54.30 lb(US) (24.63 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	

Dimensions Drawings

Dimensions

Dimensions of Motor



	mm	in.
L (without holding brake)	202	7.95
L (with holding brake)	235	9.25
A	79	3.11
С	73	2.87
D	35	1.38
F	63	2.48
N	28	1.10
М	M12	
R	30	1.18
V	10	0.39
W	10	0.39
Z	136	5.35


Product data sheet

BCH2MR3022CF6C

Performance Curves

Torque/Speed Curves with 230 V Three Phase Supply Voltage

Servo Motor with LXM28AU30●●● Servo Drive



1: Peak torque

2: Continuous torque