## **Product data sheet**

Specifications





Lexium 28

Servo motor

servo motor BCH, Lexium 28, 130mm, 500W, 6.91kg.cm<sup>2</sup>, with oil seal, with key, brake, straight connection

BCH2MM0523CF6C

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 3,278.02 USD

#### Main

Range Compatibility

**Maximum Current Irms** 

**Maximum Permanent Current** 

**Product Or Component Type** 

Device Short Name	BCH2
Complementary	
Maximum Mechanical Speed	3000 rpm
[Us] Rated Supply Voltage	220 V 110 V
Phase	Three phase Single phase
Continuous Stall Current	2.89 A
Continuous Stall Torque	21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase
Continuous Power	500 W
Peak Stall Torque	63.37 lbf.in (7.16 N.m) LXM26D 4.5 A, 220 V, single phase 63.37 lbf.in (7.16 N.m) LXM26D 4.5 A, 220 V, three phase 63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, single phase 63.37 lbf.in (7.16 N.m) LXM28 4.5 A, 220 V, three phase 63.37 lbf.in (7.16 N.m) LXM28 9 A, 110 V, single phase
Nominal Output Power	500 W LXM26D 4.5 A, 220 V, single phase 500 W LXM26D 4.5 A, 220 V, three phase 500 W LXM28 4.5 A, 220 V, single phase 500 W LXM28 4.5 A, 220 V, three phase 500 W LXM28 9 A, 110 V, single phase
Nominal Torque	21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM26D 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, single phase 21.15 lbf.in (2.39 N.m) LXM28 4.5 A, 220 V, three phase 21.15 lbf.in (2.39 N.m) LXM28 9 A, 110 V, single phase
Nominal Speed	2000 rpm LXM26D 4.5 A, 220 V, single phase 2000 rpm LXM26D 4.5 A, 220 V, three phase 2000 rpm LXM28 4.5 A, 220 V, single phase 2000 rpm LXM28 4.5 A, 220 V, three phase 2000 rpm LXM28 9 A, 110 V, single phase

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

9.18 A LXM28... 0.5 kW, 220 V 9.18 A LXM28... 0.5 kW, 110 V

3.24 A

Product Compatibility	LXM26D servo drive 0.5 kW, 220 V, single phase LXM26D servo drive 0.5 kW, 220 V, three phase LXM28 servo drive 0.5 kW, 220 V, single phase LXM28 servo drive 0.5 kW, 220 V, three phase LXM28 servo drive 0.5 kW, 110 V, single phase
Shaft End	Keyed
Shaft Diameter	0.87 in (22 mm)
Shaft Length	1.77 in (45 mm)
Key Width	0.31 in (8 mm)
Feedback Type	20 bits single turn absolute encoder
Holding Brake	With
Holding Torque	84.97 lbf.in (9.6 N.m) built-in
Mounting Support	Asian standard flange
Motor Flange Size	5.12 in (130 mm)
Electrical Connection	Connector MIL
Torque Constant	0.83 N.m/A 68 °F (20 °C)
Back Emf Constant	50 V/krpm 68 °F (20 °C)
Rotor Inertia	6.91 kg.cm²
Stator Resistance	0.62 Ohm 68 °F (20 °C)
Stator Inductance	7.4 mH 68 °F (20 °C)
Stator Electrical Time Constant	11.94 ms 68 °F (20 °C)
Maximum Radial Force Fr	670 N 2000 rpm
Maximum Axial Force Fa	200 N
Brake Pull-In Power	19.7 W
Type Of Cooling	Natural convection
Length	7.20 in (183 mm)
Number Of Motor Stacks	1
Centring Collar Diameter	4.33 in (110 mm)
Centring Collar Depth	0.31 in (8 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.36 in (9.2 mm)
Circle Diameter Of The Mounting Holes	5.71 in (145 mm)
Distance Shaft Shoulder-Flange	0.31 in (8 mm)
Net Weight	18.08 lb(US) (8.2 kg)

### **Environment**

Ip Degree Of Protection	IP50 IM V3 IP65 IM B5, IM V1
Ambient Air Temperature For Operation	32104 °F (040 °C)

# Ordering and shipping details

Category	US1PC5318281
Discount Schedule	PC53

Gtin	3606480734199
Returnability	No
Country Of Origin	CN

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.13 in (18.1 cm)
Package 1 Width	9.06 in (23 cm)
Package 1 Length	14.17 in (36 cm)
Package 1 Weight	324.51 oz (9200 g)

### Sustainability Green Premium"

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	


### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
<b>Environmental Disclosure</b>	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

#### **Dimensions Drawings**

#### **Dimensions**

#### **Dimensions of Motor**




	mm	in.
L (without holding brake)	147	5.79
L (with holding brake)	183	7.2
Z	94.5	3.72

### BCH2MM0523CF6C

#### Performance Curves

#### Torque/Speed Curves with 230 V Single/Three Phase Supply Voltage

# Servo Motor with LXM28AU04●●● Servo Drive M [Nm]



1: Peak torque

2: Continuous torque