



Overview

Model Name	APC Back-UPS Pro 500 Lithium Ion UPS
Includes	CD with software , Cat 5 ethernet cable , Installation guide , Telephone Cable , USB cable , User Manual , Wall-mounting template , Warranty card
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Bermuda , Canada , Cayman Islands , Colombia , Costa Rica , Dominican Republic , Ecuador , El Salvador , Guatemala , Haiti , Honduras , Jamaica , Mexico , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Output Power Capacity	300 Watts / 500 VA
Max Configurable Power (Watts)	300 Watts / 500 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Standby
Waveform Type	Quasi-sine Wave
Output Connections	(4) NEMA 5-15R (Battery Backup)

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	6 feet (1.83 meters)
Input Breaker Capacity	7 A

Batteries & Runtime

Battery Type	Li-ion
Typical recharge time	16 hour(s)
Replacement Battery	APCRBC146-LI
RBC Quantity	1

Communications & Management

Interface Port(s)	USB
Control panel	Network link status LED

Surge Protection and Filtering

Surge energy rating	613 Joules
Data Line Protection	RJ-11 Modem/Fax protection

Physical

Maximum Height	2.13 inches (54.0 mm)
Maximum Width	11.42 inches (290.0 mm)
Maximum Depth	7.52 inches (191.0 mm)
Net Weight	4.84 lbs (2.21 kg)
Shipping Weight	6.38 lbs (2.9 kg)
Shipping Height	3.82 inches (97.0 mm)
Shipping Width	14.57 inches (370.0 mm)
Shipping Depth	11.18 inches (284.0 mm)
Master Carton Units	2.0
Master Carton Weight	6.3 kg
Color	Black
SCC Codes	1073130429958 2
Units per Pallet	72.0
# of Layers per Pallet	3
# of Units per Layer per Pallet	24
Pallet Weight	605.0 lbs (275.0 kg)

Environmental

Operating Environment	50 - 104 °F (10 - 40 °C)
Operating Relative Humidity	10 - 90 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	10 - 90 %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	45.000 dB

Conformance

Approvals	California (CEC) Battery Charger , FCC Part 15 Class B , FCC Part 68 , UL 1778 , cTUVus
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
Battery Directive	Compliant