# **Product data sheet**

Specification





servo motor BMH, Lexium 32, 3.4Nm, 8000rpm, untapped shaft, without brake, IP65, IP67, 128 multiturn encoder

BMH0703T22A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 2,122.50 USD

## Main

<b>Device Short Name</b>	ВМН						
Product Or Component Type	Servo motor						
Maximum Mechanical Speed	8000 rpm						
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 lbf.in (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase						
Peak Stall Torque	77.00 lbf.in (8.7 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 lbf.in (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase						
Nominal Output Power	650 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase						
Nominal Torque	27.44 lbf.in (3.1 N.m) LXM32.D30M2 10 A, 115 V, single phase 25.67 lbf.in (2.9 N.m) LXM32.D18M2 6 A, 230 V, single phase						
Nominal Speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase						
Product Compatibility	LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase						
Shaft End	Smooth shaft						
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit						
Speed Feedback Resolution	131072 points/turn x 4096 turns						
Holding Brake	Without						
Mounting Support	International standard flange						
Electrical Connection	Rotatable right-angled connectors						

## Complementary

•	
Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	5.55 A
Continuous Power	1.68 W
Maximum Current Irms	15 A LXM32.D30M2 17.8 A LXM32.D18M2
Maximum Permanent Current	17.84 A
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

0.55 in (14 mm)
1.18 in (30 mm)
Multiturn SinCos Hiperface
2.76 in (70 mm)
3
0.61 N.m/A 248 °F (120 °C)
39.3 V/krpm 248 °F (120 °C)
10
1.67 kg.cm <sup>2</sup>
1.32 Ohm 68 °F (20 °C)
4.3 mH 68 °F (20 °C)
3.3 ms 68 °F (20 °C)
730 N 1000 rpm 580 N 2000 rpm 510 N 3000 rpm 460 N 4000 rpm 430 N 5000 rpm 400 N 6000 rpm
0.2 x Fr
Natural convection
7.32 in (186 mm)
2.36 in (60 mm)
0.10 in (2.5 mm)
4
0.22 in (5.5 mm)
3.23 in (82 mm)
6.61 lb(US) (3 kg)

## Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485195025
Returnability	No
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.33 in (11.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	4.85 lb(US) (2.2 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Green Premium\*

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>Ø</b>	Mercury Free	
	Rohs Exemption Information	Yes
<b>②</b>	Pvc Free	

## **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

## **BMH0703T22A2A**

## **Dimensions Drawings**

#### **Servo Motors Dimensions**

## **Example with Straight Connectors**



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)

#### Dimensions in mm

Straight Rotatable angled connectors connectors		c (without c (with		c1 c2	c2	c2 c3	h	h1	Ø	Ø1 for		
b1	b2	b1	b2	brake)	brake)							screws
39.5	25.5	39.5	39.5	186	225	30	20	5	5 h9	16 <sup>+0</sup> _ 0.13	14 k6	M5 x 17

#### Dimensions in in.

_	Straight connectors		Rotatable angled connectors		c (with brake)	c1	c2	с3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2	brake)								
1.55	1	1.55	1.55	7.32	8.85	1.18	0.78	0.19	0.20 h9	0.63 <sup>+0</sup> _ 0.0051	0.55 k6	M5 x 0.67


## **BMH0703T22A2A**

#### Performance Curves

## 115 V Single-Phase Supply Voltage

## **Torque/Speed Curves**

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

## 230 V Single-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque