# Product data sheet





servo motor BMH, Lexium 32, 3.3Nm, 6000rpm, untapped shaft, with brake, IP65, IP67, 16 multiturn encoder, straight

BMH1001P27F1A

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Servo motor			
Device Short Name	вмн			
Maximum Mechanical Speed	6000 rpm			
Continuous Stall Torque	29.21 lbf.in (3.3 N.m) LXM32.D12N4 3 A, 400 V, three phase 29.21 lbf.in (3.3 N.m) LXM32.D12N4 3 A, 480 V, three phase 30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 30.09 lbf.in (3.4 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Peak Stall Torque	95.59 lbf.in (10.8 N.m) LXM32.D12N4 3 A, 400 V, three phase 95.59 lbf.in (10.8 N.m) LXM32.D12N4 3 A, 480 V, three phase 95.59 lbf.in (10.8 N.m) LXM32.D18N4 6 A, 400 V, three phase 95.59 lbf.in (10.8 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Nominal Output Power	800 W LXM32.D12N4 3 A, 400 V, three phase 800 W LXM32.D12N4 3 A, 480 V, three phase 1300 W LXM32.D18N4 6 A, 400 V, three phase 1300 W LXM32.D18N4 6 A, 480 V, three phase			
Nominal Torque	16.82 lbf.in (1.9 N.m) LXM32.D12N4 3 A, 400 V, three phase 16.82 lbf.in (1.9 N.m) LXM32.D12N4 3 A, 480 V, three phase 27.44 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 400 V, three phase 27.44 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Nominal Speed	4000 rpm LXM32.D12N4 3 A, 400 V, three phase 4000 rpm LXM32.D12N4 3 A, 480 V, three phase 4000 rpm LXM32.D18N4 6 A, 400 V, three phase 4000 rpm LXM32.D18N4 6 A, 480 V, three phase			
Product Compatibility	LXM32.D12N4 400480 V three phase LXM32.D18N4 400480 V three phase			
Shaft End	Smooth shaft			
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit			
Speed Feedback Resolution	32768 points/turn x 4096 turns			
Holding Brake	With			
Mounting Support	International standard flange			
Electrical Connection	Straight connectors			

#### Complementary

Range Compatibility	Lexium 32		
[Us] Rated Supply Voltage	480 V		
Phase	Three phase		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Continuous Stall Current	3.15 A		
Continuous Power	1.76 W		
Maximum Current Irms	11.9 A LXM32.D12N4 11.9 A LXM32.D18N4		
Maximum Permanent Current	11.93 A		
Second Shaft	Without second shaft end		
Shaft Diameter	0.75 in (19 mm)		
Shaft Length	1.57 in (40 mm)		
Feedback Type	Multiturn SinCos Hiperface		
Holding Torque	48.68 lbf.in (5.5 N.m) holding brake		
Motor Flange Size	3.94 in (100 mm)		
Number Of Motor Stacks	1		
Torque Constant	1.1 N.m/A 248 °F (120 °C)		
Back Emf Constant	70.3 V/krpm 248 °F (120 °C)		
Number Of Motor Poles	10		
Rotor Inertia	3.68 kg.cm²		
Stator Resistance	3.1 Ohm 68 °F (20 °C)		
Stator Inductance	13.9 mH 68 °F (20 °C)		
Stator Electrical Time Constant	4.5 ms 68 °F (20 °C)		
Maximum Radial Force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Brake Pull-In Power	12 W		
Type Of Cooling	Natural convection		
Length	6.70 in (170.3 mm)		
Centring Collar Diameter	3.74 in (95 mm)		
Centring Collar Depth	0.14 in (3.5 mm)		
Number Of Mounting Holes	4		
Mounting Holes Diameter	0.35 in (9 mm)		
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)		
Net Weight	10.58 lb(US) (4.8 kg)		

# Ordering and shipping details

Category	US1PC5318282		
Discount Schedule	PC53		
Gtin	3606485195773		
Returnability	No		
Country Of Origin	DE		

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	8.66 in (22.0 cm)		
Package 1 Width	7.87 in (20.0 cm)		
Package 1 Length	15.75 in (40.0 cm)		
Package 1 Weight	11.24 lb(US) (5.1 kg)		

## **Contractual warranty**

Warranty 18 months

## Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

### BMH1001P27F1A

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

#### Dimensions in mm

Straight connectors		Rotatable angled connectors		- (i4b4 bl)	a (with handsa)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	128	170

#### Dimensions in in.


Straight connectors		Rotatable angled connectors		c (without brake)	(درامیرها والمنین)	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	5.03	6.69	

#### Performance Curves

### 400 V 3-Phase Supply Voltage


#### **Torque/Speed Curves**

Servo motor with LXM32•D12N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

### Servo motor with LXM32•D18N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage


#### **Torque/Speed Curves**

Servo motor with LXM32•D12N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque