Product data sheet





servo motor BMH, Lexium 32, 3.4Nm, 6000rpm, untapped shaft, with brake, IP54, 16bit encoder, straight

BMH1001T06F1A

! Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Servo motor			
Device Short Name	ВМН			
Maximum Mechanical Speed	6000 rpm			
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 lbf.in (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase			
Peak Stall Torque	78.77 lbf.in (8.9 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 lbf.in (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase			
Nominal Output Power	700 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase			
Nominal Torque	29.21 lbf.in (3.3 N.m) LXM32.D30M2 10 A, 115 V, single phase 24.78 lbf.in (2.8 N.m) LXM32.D18M2 6 A, 230 V, single phase			
Nominal Speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase			
Product Compatibility	LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase			
Shaft End	Smooth shaft			
Ip Degree Of Protection	IP54 standard			
Speed Feedback Resolution	32768 points/turn			
Holding Brake	With			
Mounting Support	International standard flange			
Electrical Connection	Straight connectors			

Complementary

Range Compatibility	Lexium 32		
[Us] Rated Supply Voltage	240 V		
Phase	Three phase		
Continuous Stall Current	5.11 A		
Continuous Power	1.74 W		
Maximum Current Irms	15 A LXM32.D30M2 19.4 A LXM32.D18M2		
Maximum Permanent Current	19.38 A		
Second Shaft	Without second shaft end		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)			
Shaft Length	1.57 in (40 mm)			
Feedback Type	Single turn SinCos Hiperface			
Holding Torque	48.68 lbf.in (5.5 N.m) holding brake			
Motor Flange Size	3.94 in (100 mm)			
Number Of Motor Stacks	1			
Torque Constant	0.67 N.m/A 248 °F (120 °C)			
Back Emf Constant	43.3 V/krpm 248 °F (120 °C)			
Number Of Motor Poles	10			
Rotor Inertia	3.68 kg.cm ²			
Stator Resistance	1.19 Ohm 68 °F (20 °C)			
Stator Inductance	5.3 mH 68 °F (20 °C)			
Stator Electrical Time Constant	4.5 ms 68 °F (20 °C)			
Maximum Radial Force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm			
Maximum Axial Force Fa	0.2 x Fr			
Brake Pull-In Power	12 W			
Type Of Cooling	Natural convection			
Length	6.70 in (170.3 mm)			
Centring Collar Diameter	3.74 in (95 mm)			
Centring Collar Depth	0.14 in (3.5 mm)			
Number Of Mounting Holes	4			
Mounting Holes Diameter	0.35 in (9 mm)			
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)			
Net Weight	10.58 lb(US) (4.8 kg)			

Ordering and shipping details

	• • •
Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485197029
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	7.68 in (19.5 cm)		
Package 1 Width	8.66 in (22.0 cm)		
Package 1 Length	15.75 in (40.0 cm)		
Package 1 Weight	11.41 lb(US) (5.174 kg)		

Contractual warranty

Warranty

Apr 19, 2024

18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

BMH1001T06F1A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight connectors		Rotatable angled connectors		- (i4b4 bl)	a (with hands)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	128	170

Dimensions in in.

Zimonono in ini						
Straight connectors		Rotatable angled connectors		c (without brake)	a (with brake)	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	5.03	6.69	

Product data sheet


BMH1001T06F1A

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque