Product data sheet

Specifications





servo motor BMH, Lexium 32, 6.2Nm, 6000rpm, untapped shaft, without brake, IP54, 16 multiturn encoder, straight

BMH1002P07A1A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,415.00 USD

Main

Servo motor			
ВМН			
6000 rpm			
54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 400 V, three phase 54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 480 V, three phase			
162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 480 V, three phase			
1600 W LXM32.D18N4 6 A, 400 V, three phase 1600 W LXM32.D18N4 6 A, 480 V, three phase			
34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 400 V, three phase 34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 480 V, three phase			
4000 rpm LXM32.D18N4 6 A, 400 V, three phase 4000 rpm LXM32.D18N4 6 A, 480 V, three phase			
LXM32.D18N4 400480 V three phase			
Smooth shaft			
IP54 standard			
32768 points/turn x 4096 turns			
Without			
International standard flange			
Straight connectors			

Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	480 V
Phase	Three phase
Continuous Stall Current	5.04 A
Continuous Power	2.36 W
Maximum Current Irms	18 A LXM32.D18N4
Maximum Permanent Current	18.23 A
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Length	1.57 in (40 mm)		
Feedback Type	Multiturn SinCos Hiperface		
Motor Flange Size	3.94 in (100 mm)		
Number Of Motor Stacks	2		
Torque Constant	1.2 N.m/A 248 °F (120 °C)		
Back Emf Constant	77 V/krpm 248 °F (120 °C)		
Number Of Motor Poles	10		
Rotor Inertia	6.28 kg.cm ²		
Stator Resistance	1.51 Ohm 68 °F (20 °C)		
Stator Inductance	7.5 mH 68 °F (20 °C)		
Stator Electrical Time Constant	5 ms 68 °F (20 °C)		
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Type Of Cooling	Natural convection		
Length	6.32 in (160.6 mm)		
Centring Collar Diameter	3.74 in (95 mm)		
Centring Collar Depth	0.14 in (3.5 mm)		
Number Of Mounting Holes	4		
Mounting Holes Diameter	0.35 in (9 mm)		
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)		
Net Weight	10.85 lb(US) (4.92 kg)		

Ordering and shipping details

Category	US1PC5318282		
Discount Schedule	PC53		
Gtin	3606485196183		
Returnability	No		
Country Of Origin	DE		

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.66 in (22.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	11.51 lb(US) (5.22 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Circularity Profile	No need of specific recycling operations		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



a: Power supply for servo motor brake

b: Power supply for servo motor encoder

- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight c	onnectors	Rotatable angled connectors		a (without braka)	o (with broko)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	160	202

Dimensions in in.


Straight connectors		Rotatable angled connectors		a (without braka)	o (with broko)
b1	b2	b1	b2	c (without brake)	c (with brake)
1.55	1.00	1.55	1.55	6.29	7.95

Performance Curves

400 V 3-Phase Supply Voltage

Torque/Speed Curves


Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque