# **Product data sheet**

Specifications





servo motor BMH, Lexium 32, 3.4Nm, 6000rpm, keyed shaft, without brake, IP54, 128bit encoder, straight

BMH1001T11A1A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,785.00 USD

#### Main

Product Or Component Type	Servo motor				
Device Short Name	ВМН				
Maximum Mechanical Speed	6000 rpm				
Continuous Stall Torque	30.09 lbf.in (3.4 N.m) LXM32.D30M2 10 A, 115 V, single phase 30.09 lbf.in (3.4 N.m) LXM32.D18M2 6 A, 230 V, single phase				
Peak Stall Torque	78.77 lbf.in (8.9 N.m) LXM32.D30M2 10 A, 115 V, single phase 90.28 lbf.in (10.2 N.m) LXM32.D18M2 6 A, 230 V, single phase				
Nominal Output Power	700 W LXM32.D30M2 10 A, 115 V, single phase 900 W LXM32.D18M2 6 A, 230 V, single phase				
Nominal Torque	29.21 lbf.in (3.3 N.m) LXM32.D30M2 10 A, 115 V, single phase 24.78 lbf.in (2.8 N.m) LXM32.D18M2 6 A, 230 V, single phase				
Nominal Speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D18M2 6 A, 230 V, single phase				
Product Compatibility	LXM32.D30M2 115 V single phase LXM32.D18M2 230 V single phase				
Shaft End	Keyed				
Ip Degree Of Protection	IP54 standard				
Speed Feedback Resolution	131072 points/turn				
Holding Brake Without					
Mounting Support	International standard flange				
Electrical Connection	Straight connectors				

## Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	5.11 A
Continuous Power	1.74 W
Maximum Current Irms	15 A LXM32.D30M2 19.4 A LXM32.D18M2
Maximum Permanent Current	19.38 A
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)		
Shaft Length	1.57 in (40 mm)		
Key Width	1.18 in (30 mm)		
Feedback Type	Single turn SinCos Hiperface		
Motor Flange Size	3.94 in (100 mm)		
Number Of Motor Stacks	1		
Torque Constant	0.67 N.m/A 248 °F (120 °C)		
Back Emf Constant	43.3 V/krpm 248 °F (120 °C)		
Number Of Motor Poles	10		
Rotor Inertia	3.19 kg.cm²		
Stator Resistance	1.19 Ohm 68 °F (20 °C)		
Stator Inductance	5.3 mH 68 °F (20 °C)		
Stator Electrical Time Constant	4.5 ms 68 °F (20 °C)		
Maximum Radial Force Fr	900 N 1000 rpm 720 N 2000 rpm 630 N 3000 rpm 570 N 4000 rpm 530 N 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Type Of Cooling	Natural convection		
Length	5.06 in (128.6 mm)		
Centring Collar Diameter	3.74 in (95 mm)		
Centring Collar Depth	0.14 in (3.5 mm)		
Number Of Mounting Holes	4		
Mounting Holes Diameter	0.35 in (9 mm)		
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)		
Net Weight	7.36 lb(US) (3.34 kg)		

# Ordering and shipping details

_	
Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485200651
Returnability	No
Country Of Origin	DE

# **Packing Units**

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	7.87 in (20.0 cm)		
Package 1 Width	8.66 in (22.0 cm)		
Package 1 Length	15.75 in (40.0 cm)		
Package 1 Weight	8.02 lb(US) (3.64 kg)		

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



#### **Certifications & Standards**


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

### BMH1001T11A1A

#### **Dimensions Drawings**

#### **Servo Motors Dimensions**

#### **Example with Straight Connectors**



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

#### Dimensions in mm

Straight connectors		Rotatable angled connectors		a (with and bunks)	a (with handsa)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	128	170

#### Dimensions in in.

Straight connectors		Rotatable angled connectors		c (without brake)	( د ا د ا د ا د ا د ا	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	5.03	6.69	

### Product data sheet


### BMH1001T11A1A

#### Performance Curves

### 115 V Single-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 230 V Single-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D18M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque