# Product data sheet

Specifications





## servo motor BMH, Lexium 32, 6.2Nm, 6000rpm, keyed shaft, without brake, IP54, 16bit encoder

BMH1002P16A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

## Price\*: 1,185.00 USD

## Main

Product Or Component Type	Servo motor			
Device Short Name	ВМН			
Maximum Mechanical Speed	6000 rpm			
Continuous Stall Torque	54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 400 V, three phase 54.87 lbf.in (6.2 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Peak Stall Torque	162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 400 V, three phase 162.85 lbf.in (18.4 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Nominal Output Power	1600 W LXM32.D18N4 6 A, 400 V, three phase 1600 W LXM32.D18N4 6 A, 480 V, three phase			
Nominal Torque	34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 400 V, three phase 34.52 lbf.in (3.9 N.m) LXM32.D18N4 6 A, 480 V, three phase			
Nominal Speed	4000 rpm LXM32.D18N4 6 A, 400 V, three phase 4000 rpm LXM32.D18N4 6 A, 480 V, three phase			
Product Compatibility	LXM32.D18N4 400480 V three phase			
Shaft End	Keyed			
Ip Degree Of Protection	IP54 standard			
Speed Feedback Resolution	32768 points/turn			
Holding Brake	Without			
Mounting Support	International standard flange			
Electrical Connection	Rotatable right-angled connectors			

## Complementary

Range Compatibility	Lexium 32			
[Us] Rated Supply Voltage	480 V			
Phase	Three phase			
Continuous Stall Current	5.04 A			
Continuous Power	2.36 W			
Maximum Current Irms	18 A LXM32.D18N4			
Maximum Permanent Current	18.23 A			
Second Shaft	Without second shaft end			
Shaft Diameter	0.75 in (19 mm)			
Shaft Length	1.57 in (40 mm)			

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Key Width	1.18 in (30 mm)		
Feedback Type	Single turn SinCos Hiperface		
Motor Flange Size	3.94 in (100 mm)		
Number Of Motor Stacks	2		
Torque Constant	1.2 N.m/A 248 °F (120 °C)		
Back Emf Constant	77 V/krpm 248 °F (120 °C)		
Number Of Motor Poles	10		
Rotor Inertia	6.28 kg.cm <sup>2</sup>		
Stator Resistance	1.51 Ohm 68 °F (20 °C)		
Stator Inductance	7.5 mH 68 °F (20 °C)		
Stator Electrical Time Constant	5 ms 68 °F (20 °C)		
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm		
Maximum Axial Force Fa	0.2 x Fr		
Type Of Cooling	Natural convection		
Length	6.32 in (160.6 mm)		
Centring Collar Diameter	3.74 in (95 mm)		
Centring Collar Depth	0.14 in (3.5 mm)		
Number Of Mounting Holes	4		
Mounting Holes Diameter	0.35 in (9 mm)		
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)		
Net Weight	10.85 lb(US) (4.92 kg)		

## Ordering and shipping details

Category	US1PC5318282		
Discount Schedule	PC53		
Gtin	3606485196114		
Returnability	Yes		
Country Of Origin	US		

## **Packing Units**

-				
Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	8.66 in (22.000 cm)			
Package 1 Width	7.68 in (19.500 cm)			
Package 1 Length	15.75 in (40.000 cm)			
Package 1 Weight	13.26 lb(US) (6.014 kg)			
Unit Type Of Package 2	P06			
Number Of Units In Package 2	12			
Package 2 Height	41.34 in (105.000 cm)			

2

Package 2 Width	23.62 in (60.000 cm)	
Package 2 Length	31.50 in (80.000 cm)	
Package 2 Weight	179.17 lb(US) (81.268 kg)	

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


### **Certifications & Standards**

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

### **Dimensions Drawings**

#### **Servo Motors Dimensions**

### **Example with Straight Connectors**



a: Power supply for servo motor brake

b: Power supply for servo motor encoder

- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight c	Straight connectors Rotatable angled connectors				
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	160	202

Dimensions in in.


Straight connectors		Rotatable angled connectors			e (with broke)
b1	b2	b1	b2	c (without brake)	c (with brake)
1.55	1.00	1.55	1.55	6.29	7.95

### Performance Curves

### 400 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

#### 480 V 3-Phase Supply Voltage

#### **Torque/Speed Curves**



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque