Product data sheet

Specification





servo motor BMH, Lexium 32, 6Nm, 6000rpm, keyed shaft, without brake, IP65, IP67, 16 multiturn encoder

BMH1002T37A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,302.50 USD

Main

Product Or Component Type	Servo motor				
Device Short Name	вмн				
Maximum Mechanical Speed	6000 rpm				
Continuous Stall Torque	53.10 lbf.in (6 N.m) LXM32.D30M2 10 A, 115 V, single phase 53.10 lbf.in (6 N.m) LXM32.D30M2 10 A, 230 V, single phase				
Peak Stall Torque	91.16 lbf.in (10.3 N.m) LXM32.D30M2 10 A, 115 V, single phase 162.85 lbf.in (18.4 N.m) LXM32.D30M2 10 A, 230 V, single phase				
Nominal Output Power	750 W LXM32.D30M2 10 A, 115 V, single phase 1450 W LXM32.D30M2 10 A, 230 V, single phase				
Nominal Torque	30.98 lbf.in (3.5 N.m) LXM32.D30M2 10 A, 115 V, single phase 40.71 lbf.in (4.6 N.m) LXM32.D30M2 10 A, 230 V, single phase				
Nominal Speed	2000 rpm LXM32.D30M2 10 A, 115 V, single phase 3000 rpm LXM32.D30M2 10 A, 230 V, single phase				
Product Compatibility	LXM32.D30M2 115 V single phase LXM32.D30M2 230 V single phase				
Shaft End	Keyed				
Ip Degree Of Protection	IP65 standard IP67 with IP67 kit				
Speed Feedback Resolution	32768 points/turn x 4096 turns				
Holding Brake	Without				
Mounting Support International standard flange					
Electrical Connection Rotatable right-angled connectors					

Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	8.65 A
Continuous Power	2.39 W
Maximum Current Irms	15 A LXM32.D30M2 115 V 30 A LXM32.D30M2 230 V
Maximum Permanent Current	30.24 A
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)			
Shaft Length	1.57 in (40 mm)			
Key Width	1.18 in (30 mm)			
Feedback Type	Multiturn SinCos Hiperface			
Motor Flange Size	3.94 in (100 mm)			
Number Of Motor Stacks	2			
Torque Constant	0.72 N.m/A 248 °F (120 °C)			
Back Emf Constant	46.2 V/krpm 248 °F (120 °C)			
Number Of Motor Poles	10			
Rotor Inertia	6.28 kg.cm ²			
Stator Resistance	0.54 Ohm 68 °F (20 °C)			
Stator Inductance	2.7 mH 68 °F (20 °C)			
Stator Electrical Time Constant	5 ms 68 °F (20 °C)			
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm			
Maximum Axial Force Fa	0.2 x Fr			
Type Of Cooling	Natural convection			
Length	6.32 in (160.6 mm)			
Centring Collar Diameter	3.74 in (95 mm)			
Centring Collar Depth	0.14 in (3.5 mm)			
Number Of Mounting Holes	4			
Mounting Holes Diameter	0.35 in (9 mm)			
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)			
Net Weight	10.85 lb(US) (4.92 kg)			

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485197715
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE		
Number Of Units In Package 1	1		
Package 1 Height	8.66 in (22.0 cm)		
Package 1 Width	7.87 in (20.0 cm)		
Package 1 Length	15.75 in (40.0 cm)		
Package 1 Weight	11.51 lb(US) (5.22 kg)		

Contractual warranty

Warranty

Apr 26, 2024

18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

BMH1002T37A2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight connectors		Rotatable angled connectors		a (with and bunks)	a (with handsa)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	160	202

Dimensions in in.


Straight connectors		Rotatable angled connectors		c (without brake)	a (with brake)	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	6.29	7.95	

Performance Curves

115 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque