Product data sheet

Specifications





servo motor BMH, Lexium 32, 8.2Nm, 6000rpm, untapped shaft, without brake, IP54, 128 multiturn encoder

BMH1003T02A2A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 4,117.50 USD

Main

Product Or Component Type	Servo motor		
Device Short Name	ВМН		
Maximum Mechanical Speed	6000 rpm		
Continuous Stall Torque	72.58 lbf.in (8.2 N.m) LXM32.D30M2 10 A, 230 V, single phase		
Peak Stall Torque	201.80 lbf.in (22.8 N.m) LXM32.D30M2 10 A, 230 V, single phase		
Nominal Output Power	1450 W LXM32.D30M2 10 A, 230 V, single phase		
Nominal Torque	49.56 lbf.in (5.6 N.m) LXM32.D30M2 10 A, 230 V, single phase		
Nominal Speed	2500 rpm LXM32.D30M2 10 A, 230 V, single phase		
Product Compatibility	LXM32.D30M2 230 V single phase		
Shaft End	Smooth shaft		
Ip Degree Of Protection	IP54 standard		
Speed Feedback Resolution	131072 points/turn x 4096 turns		
Holding Brake	Without		
Mounting Support	International standard flange		
Electrical Connection	Rotatable right-angled connectors		

Complementary

Range Compatibility	Lexium 32
[Us] Rated Supply Voltage	240 V
Phase	Three phase
Continuous Stall Current	10 A
Continuous Power	2.62 W
Maximum Current Irms	30 A LXM32.D30M2
Maximum Permanent Current	33.85 A
Second Shaft	Without second shaft end
Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Feedback Type	Multiturn SinCos Hiperface
Motor Flange Size	3.94 in (100 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Motor Stacks	3			
Torque Constant	0.851 N.m/A 248 °F (120 °C)			
Back Emf Constant	54.8 V/krpm 248 °F (120 °C)			
Number Of Motor Poles	10			
Rotor Inertia	9.37 kg.cm²			
Stator Resistance	0.47 Ohm 68 °F (20 °C)			
Stator Inductance	3 mH 68 °F (20 °C)			
Stator Electrical Time Constant	6.4 ms 68 °F (20 °C)			
Maximum Radial Force Fr	1050 N 1000 rpm 830 N 2000 rpm 730 N 3000 rpm 660 N 4000 rpm 610 N 5000 rpm			
Maximum Axial Force Fa	0.2 x Fr			
Type Of Cooling	Natural convection			
Length	7.58 in (192.6 mm)			
Centring Collar Diameter	3.74 in (95 mm)			
Centring Collar Depth	0.14 in (3.5 mm)			
Number Of Mounting Holes	4			
Mounting Holes Diameter	0.35 in (9 mm)			
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)			
Net Weight	14.33 lb(US) (6.5 kg)			

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3606485197845
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.66 in (22.0 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	15.75 in (40.0 cm)
Package 1 Weight	14.99 lb(US) (6.8 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

BMH1003T02A2A

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
- b: Power supply for servo motor encoder
- (1) Shaft end, keyed slot (optional)
- (2) For screw M6 x 21 mm/M6 x 0.83 in.

Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	a (with brake)
b1	b2	b1	b2	c (without brake)	c (with brake)
39.5	25.5	39.5	39.5	192	234

Dimensions in in


Zimonono in im						
Straight connectors		Rotatable angled connectors		c (without brake)	المام	
b1	b2	b1	b2	c (without brake)	c (with brake)	
1.55	1.00	1.55	1.55	7.55	9.21	

Performance Curves

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque