Product data sheet

Specification





servo motor BMI 3-phase untapped IP65 multiturn - 131072 p/t x 4096 t

BMI1002P22A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,225.64 USD

Main

Range Compatibility	Lexium 32i	
Product Or Component Type	Servo motor with power stage	
Device Short Name	BMI	

Complementary

Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	208480 V - 1510 %
Supply Voltage Limits	208480 V
Phase	Three phase
Supply Frequency	50/60 Hz - 55 %
Network Frequency Limits	47.563 Hz
Emc Filter	Integrated
Continuous Output Current	4 A 8 kHz
Output Current 3S Peak	12 A 400 V 3 s
Continuous Stall Current	4 A
Continuous Stall Torque	53.10 lbf.in (6 N.m) 208480 V three phase
Peak Stall Torque	123.91 lbf.in (14 N.m) 208 V three phase 123.91 lbf.in (14 N.m) 400 V three phase 123.91 lbf.in (14 N.m) 480 V three phase
Nominal Output Power	1000 W 208 V three phase 1900 W 400 V three phase 1900 W 480 V three phase
Nominal Torque	45.14 lbf.in (5.1 N.m) 400 V three phase 47.79 lbf.in (5.4 N.m) 208 V three phase 36.29 lbf.in (4.1 N.m) 480 V three phase
Nominal Speed	1900 rpm 208 V three phase 3800 rpm 400 V three phase 4700 rpm 480 V three phase
Maximum Current Irms	17.5 A 208 V, three phase 17.5 A 400 V, three phase 17.5 A 480 V, three phase
Product Compatibility	Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT
Shaft End	Untapped
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)	
Shaft Length	1.57 in (40 mm)	
Feedback Type	Absolute multiturn SinCos Hiperface	
Speed Feedback Resolution	131072 points/turn x 4096 turns	
Holding Brake	Without	
Mounting Support	International standard flange	
Motor Flange Size	3.94 in (100 mm)	
Electrical Connection	Printed circuit board connector	
Torque Constant	1.28 N.m/A 68 °F (20 °C)	
Back Emf Constant	84.52 V/krpm 68 °F (20 °C)	
Number Of Motor Poles	10	
Rotor Inertia	6.28 kg.cm²	
Stator Resistance	2.347 Ohm 68 °F (20 °C)	
Stator Inductance	9.79 mH 68 °F (20 °C)	
Stator Electrical Time Constant	4.17 ms 68 °F (20 °C)	
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm	
Maximum Axial Force Fa	0.2 x Fr	
Type Of Cooling	Natural convection	
Length	10.75 in (273 mm)	
Number Of Motor Stacks	2	
Centring Collar Diameter	3.74 in (95 mm)	
Centring Collar Depth	0.14 in (3.5 mm)	
Number Of Mounting Holes	4	
Mounting Holes Diameter	0.35 in (9 mm)	
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)	
Distance Shaft Shoulder-Flange	0.14 in (3.5 mm)	

Environment

Ip Degree Of Protection IP65

Ordering and shipping details

Category	US1PC5618287
Discount Schedule	PC56
Gtin	3606485377100
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1 PCE

Number Of Units In Package 1	1
Package 1 Height	9.84 in (25.0 cm)
Package 1 Width	7.32 in (18.6 cm)
Package 1 Length	21.65 in (55.0 cm)
Package 1 Weight	20.94 lb(US) (9.5 kg)

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
Circularity Profile	End of Life Information	

Dimensions Drawings

External Dimensions

With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


Dimensions in mm

Difficitations in mini			
W	Н	L	
132,6	217	294	

Dimensions in in.

W	Н	L
5,22	8,54	11,57

Mounting type B



- (1) Module for supply voltage
- (2) I/O module

(3) Standard braking resistor


Dimei	nsions	in	mm

W	Н	L
132,6	168	343

Dimensions in in.

W	Н	L
5,22	6,61	13,5

With External Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L
132,6	217	306


Dimensions in in.

W	Н	L	
5,22	8,54	12,05	

Mounting type D

Product data sheet

BMI1002P22A




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

Difficusions in mini				
W	H L			
132,6	180	343		

Dimensions in in.

Difficitional in in.				
W	Н	L		
5,22	7,09	13,5		



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


Dimensions in mm

W	Н	L
132,6	217	333

Dimensions in in.

W	H L	
5,22	8,54	13,11

Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

Difficitations in thirt				
W	Н	L		
132,6	206,5	343		


Dimensions in in.

W H I					
5,22	8,13	13,5			

Performance Curves

Performance Curves

Torque/Speed Curves with 208 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2499 W	1740 rpm	13.72 N.m
max Cont. Power (Drive)	•	1109	2160 rpm	4.90 N.m

Performance Curves

Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		5090 W	3600 rpm	13.50 N.m
max Cont. Power (Drive)	•	1954 W	4320 rpm	4.32 N.m

Performance Curves

Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		6117 W	4380 rpm	13.34 N.m
max Cont. Power (Drive)	•	2080 W	5040 rpm	3.94 N.m