Specifications





## servo motor BMI 3-phase untapped IP54 multiturn - 32768 p/ t x 4096 t - brake

BMI1002P07F

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 2,232.76 USD

### Main

Lexium 32i
Servo motor with power stage
ВМІ
6000 rpm
208480 V - 1510 %
208480 V
Three phase
50/60 Hz - 55 %
47.563 Hz
Integrated
4 A 8 kHz
12 A 400 V 3 s
4 A
53.10 lbf.in (6 N.m) 208480 V three phase
123.91 lbf.in (14 N.m) 208 V three phase 123.91 lbf.in (14 N.m) 400 V three phase 123.91 lbf.in (14 N.m) 480 V three phase
1000 W 208 V three phase 1900 W 400 V three phase 1900 W 480 V three phase
45.14 lbf.in (5.1 N.m) 400 V three phase 47.79 lbf.in (5.4 N.m) 208 V three phase 36.29 lbf.in (4.1 N.m) 480 V three phase
1900 rpm 208 V three phase 3800 rpm 400 V three phase 4700 rpm 480 V three phase
17.5 A 208 V, three phase 17.5 A 400 V, three phase 17.5 A 480 V, three phase
Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT
Untapped
Without second shaft end

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Feedback Type	Absolute multiturn SinCos Hiperface
Speed Feedback Resolution	32768 points/turn x 4096 turns
Holding Brake	With
Holding Torque	48.68 lbf.in (5.5 N.m) holding brake
Mounting Support	International standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Printed circuit board connector
Torque Constant	1.28 N.m/A 68 °F (20 °C)
Back Emf Constant	84.52 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	6.77 kg.cm <sup>2</sup>
Stator Resistance	2.347 Ohm 68 °F (20 °C)
Stator Inductance	9.79 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.17 ms 68 °F (20 °C)
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	8 W
Type Of Cooling	Natural convection
Length	11.10 in (282 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Distance Shaft Shoulder-Flange	0.14 in (3.5 mm)

### Environment

Ip Degree Of Protection

Shaft IP54 Housing IP65

## Ordering and shipping details

Category	US1PC5618287
Discount Schedule	PC56
Gtin	3606485376998
Returnability	No
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.16 in (25.8 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	23.23 in (59.0 cm)
Package 1 Weight	20.94 lb(US) (9.5 kg)
Unit Type Of Package 2	P06
Number Of Units In Package 2	8
Package 2 Height	30.31 in (77.0 cm)
Package 2 Width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	186.29 lb(US) (84.5 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance




### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Circularity Profile	End of Life Information		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth		

#### **Dimensions Drawings**

#### **External Dimensions**

## With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


#### Dimensions in mm

W	Н	L	
132,6	217	337	

#### Dimensions in in.

W	Н	L
5,22	8,54	13,27

#### Mounting type B




(2) I/O module

#### (3) Standard braking resistor

Dimensions in mm					
W H L					
132,6	132,6 168 386				

Dimensions in in.			
W H L			
5,22	6,61	15,2	

#### With External Braking Resistor



(1) Module for supply voltage

- (2) I/O module
- (4) External braking resistor


#### Dimensions in mm

W	Н	L	
132,6	217	349	

Dimensions in in.

W	Н	L
5,22	8,54	13,74

#### Mounting type D



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


Dimer	nsions	in	mm

W	Н	L
132,6	180	386

Dimensions in in.

W	н	L
5,22	7,09	15,2

#### Mounting type E




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L	
132,6	217	376	

Dimensions in in.					
W H L					
5,22	8,54	14,8			

#### Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm

W	Н	L	
132,6	206,5	386	


#### Dimensions in in.

W	Н	L	
5,22	8,13	15,2	

BMI1002P07F

Performance Curves

Performance Curves




### Torque/Speed Curves with 208 V Three Phases Supply Voltage

- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2499 W	1740 rpm	13.72 N.m
max Cont. Power (Drive)	•	1109	2160 rpm	4.90 N.m

#### Performance Curves

#### Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		5090 W	3600 rpm	13.50 N.m
max Cont. Power (Drive)	•	1954 W	4320 rpm	4.32 N.m

#### Performance Curves

#### Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		6117 W	4380 rpm	13.34 N.m
max Cont. Power (Drive)	•	2080 W	5040 rpm	3.94 N.m