Specifications





## servo motor BMI 3-phase untapped IP65 single turn -131072 p/t

BMI1002P21A

Product availability: Non-Stock - Not normally stocked in distribution facility

### Price\*: 2,026.54 USD

### Main

Range Compatibility	Lexium 32i
Product Or Component Type	Servo motor with power stage
Device Short Name	BMI
Complementary	
Maximum Mechanical Speed	6000 rpm
[Us] Rated Supply Voltage	208480 V - 1510 %
Supply Voltage Limits	208480 V
Phase	Three phase
Supply Frequency	50/60 Hz - 55 %
Network Frequency Limits	47.563 Hz
Emc Filter	Integrated
Continuous Output Current	4 A 8 kHz
Output Current 3S Peak	12 A 400 V 3 s
Continuous Stall Current	4 A
Continuous Stall Torque	53.10 lbf.in (6 N.m) 208480 V three phase
Peak Stall Torque	123.91 lbf.in (14 N.m) 208 V three phase 123.91 lbf.in (14 N.m) 400 V three phase 123.91 lbf.in (14 N.m) 480 V three phase
Nominal Output Power	1000 W 208 V three phase 1900 W 400 V three phase 1900 W 480 V three phase
Nominal Torque	45.14 lbf.in (5.1 N.m) 400 V three phase 47.79 lbf.in (5.4 N.m) 208 V three phase 36.29 lbf.in (4.1 N.m) 480 V three phase
Nominal Speed	1900 rpm 208 V three phase 3800 rpm 400 V three phase 4700 rpm 480 V three phase
Maximum Current Irms	17.5 A 208 V, three phase 17.5 A 400 V, three phase 17.5 A 480 V, three phase
Product Compatibility	Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT
Shaft End	Untapped
Second Shaft	Without second shaft end

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Shaft Diameter	0.75 in (19 mm)
Shaft Length	1.57 in (40 mm)
Feedback Type	Absolute single turn SinCos Hiperface
Speed Feedback Resolution	131072 points/turn
Holding Brake	Without
Mounting Support	International standard flange
Motor Flange Size	3.94 in (100 mm)
Electrical Connection	Printed circuit board connector
Torque Constant	1.28 N.m/A 68 °F (20 °C)
Back Emf Constant	84.52 V/krpm 68 °F (20 °C)
Number Of Motor Poles	10
Rotor Inertia	6.28 kg.cm <sup>2</sup>
Stator Resistance	2.347 Ohm 68 °F (20 °C)
Stator Inductance	9.79 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.17 ms 68 °F (20 °C)
Maximum Radial Force Fr	990 N 1000 rpm 790 N 2000 rpm 690 N 3000 rpm 620 N 4000 rpm 580 N 5000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	10.75 in (273 mm)
Number Of Motor Stacks	2
Centring Collar Diameter	3.74 in (95 mm)
Centring Collar Depth	0.14 in (3.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.35 in (9 mm)
Circle Diameter Of The Mounting Holes	4.53 in (115 mm)
Distance Shaft Shoulder-Flange	0.14 in (3.5 mm)

### Environment

Ip Degree Of Protection

IP65

## Ordering and shipping details

Category	US1PC5618287
Discount Schedule	PC56
Gtin	3606485377087
Returnability	No
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1

PCE

Number Of Units In Package 1	1
Package 1 Height	9.84 in (25.0 cm)
Package 1 Width	7.32 in (18.6 cm)
Package 1 Length	21.65 in (55.0 cm)
Package 1 Weight	20.94 lb(US) (9.5 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance




### **Certifications & Standards**

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Circularity Profile	End of Life Information		
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth		

#### **Dimensions Drawings**

#### **External Dimensions**

## With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


#### Dimensions in mm

W	Н	L
132,6	217	294

#### Dimensions in in.

W	Н	L
5,22	8,54	11,57

#### Mounting type B




(2) I/O module

#### (3) Standard braking resistor

Dimensions in mm				
W H L				
132,6	168	343		

Dimensions in in.			
W H L			
5,22	6,61	13,5	

#### With External Braking Resistor



(1) Module for supply voltage

- (2) I/O module
- (4) External braking resistor


#### Dimensions in mm

W	Н	L
132,6	217	306

Dimensions in in.

W	Н	L	
5,22	8,54	12,05	

#### Mounting type D



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


	Dimen	sions	in	mm
--	-------	-------	----	----

W	Н	L
132,6	180	343

Dimensions in in.

W	Н	L	
5,22	7,09	13,5	

#### Mounting type E




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

W	Н	L	
132,6	217	333	

Dimensions in in.						
W H L						
5,22	8,54	13,11				

#### Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

#### Dimensions in mm

W	Н	L	
132,6	206,5	343	


#### Dimensions in in.

W	Н	L
5,22	8,13	13,5

BMI1002P21A

Performance Curves

**Performance Curves** 




### Torque/Speed Curves with 208 V Three Phases Supply Voltage

- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		2499 W	1740 rpm	13.72 N.m
max Cont. Power (Drive)	•	1109	2160 rpm	4.90 N.m

#### Performance Curves

#### Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		5090 W	3600 rpm	13.50 N.m
max Cont. Power (Drive)	•	1954 W	4320 rpm	4.32 N.m

#### Performance Curves

#### Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

		Power	At Speed	With Torque
max. Peak Power		6117 W	4380 rpm	13.34 N.m
max Cont. Power (Drive)	•	2080 W	5040 rpm	3.94 N.m