Specifications





servo motor BMI 3-phase - keyed IP54 multiturn - 32768 p/t x 4096 t

BMI1003P17A

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,562.45 USD

Main

| Range Compatibility | Lexium 32i | |
|---------------------------|------------------------------|--|
| Product Or Component Type | Servo motor with power stage | |
| Device Short Name | BMI | |

Complementary

| oompicinental y | | |
|---------------------------|--|--|
| Maximum Mechanical Speed | 6000 rpm | |
| [Us] Rated Supply Voltage | 208480 V - 1510 % | |
| Supply Voltage Limits | 208480 V | |
| Phase | Three phase | |
| Supply Frequency | 50/60 Hz - 55 % | |
| Network Frequency Limits | 47.563 Hz | |
| Emc Filter | Integrated | |
| Continuous Output Current | 4 A 8 kHz | |
| Output Current 3S Peak | 12 A 400 V 3 s | |
| Continuous Stall Current | 4 A | |
| Continuous Stall Torque | 75.23 lbf.in (8.5 N.m) 208480 V three phase | |
| Peak Stall Torque | 169.93 lbf.in (19.2 N.m) 400 V three phase 169.93 lbf.in (19.2 N.m) 480 V three phase 169.93 lbf.in (19.2 N.m) 208 V three phase | |
| Nominal Output Power | 1000 W 208 V three phase 2000 W 400 V three phase 2100 W 480 V three phase | |
| Nominal Torque | 63.73 lbf.in (7.2 N.m) 208 V three phase 60.18 lbf.in (6.8 N.m) 400 V three phase 49.56 lbf.in (5.6 N.m) 480 V three phase | |
| Nominal Speed | 1500 rpm 208 V three phase 3000 rpm 400 V three phase 3700 rpm 480 V three phase | |
| Maximum Current Irms | 26.7 A 208 V, three phase 26.7 A 400 V, three phase 26.7 A 480 V, three phase | |
| Product Compatibility | Drive control unit LXM32i CANopen Drive control unit LXM32i EtherCAT | |
| Shaft End | Keyed | |
| Second Shaft | Without second shaft end | |
| Shaft Diameter | 0.75 in (19 mm) | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Shaft Length | 1.57 in (40 mm) | |
|--|---|--|
| Key Width | 0.24 in (6 mm) | |
| Feedback Type | Absolute multiturn SinCos Hiperface | |
| Speed Feedback Resolution | 32768 points/turn x 4096 turns | |
| Holding Brake | Without | |
| Mounting Support | International standard flange | |
| Motor Flange Size | 3.94 in (100 mm) | |
| Electrical Connection | Printed circuit board connector | |
| Torque Constant | 1.7 N.m/A 68 °F (20 °C) | |
| Back Emf Constant | 112 V/krpm 68 °F (20 °C) | |
| Number Of Motor Poles | 10 | |
| Rotor Inertia | 9.37 kg.cm ² | |
| Stator Resistance | 2.31 Ohm 68 °F (20 °C) | |
| Stator Inductance | 11.43 mH 68 °F (20 °C) | |
| Stator Electrical Time Constant | 4.95 ms 68 °F (20 °C) | |
| Maximum Radial Force Fr | 1050 N 1000 rpm 830 N 2000 rpm 730 N 3000 rpm 660 N 4000 rpm 610 N 5000 rpm | |
| Maximum Axial Force Fa | 0.2 x Fr | |
| Type Of Cooling | Natural convection | |
| Length | 11.77 in (299 mm) | |
| Number Of Motor Stacks | 3 | |
| Centring Collar Diameter | 3.74 in (95 mm) | |
| Centring Collar Depth | 0.14 in (3.5 mm) | |
| Number Of Mounting Holes | 4 | |
| Mounting Holes Diameter | 0.35 in (9 mm) | |
| Circle Diameter Of The Mounting Holes | 4.53 in (115 mm) | |
| Distance Shaft Shoulder-Flange | 0.14 in (3.5 mm) | |

Environment

Ip Degree Of Protection

Shaft IP54 Housing IP65

PCE

Ordering and shipping details

| Category | US1PC5618287 |
|-------------------|---------------|
| Discount Schedule | PC56 |
| Gtin | 3606485377704 |
| Returnability | No |
| Country Of Origin | DE |

Packing Units

Unit Type Of Package 1

| Number Of Units In Package 1 | 1 |
|------------------------------|------------------------|
| Package 1 Height | 9.84 in (25.0 cm) |
| Package 1 Width | 7.32 in (18.6 cm) |
| Package 1 Length | 21.65 in (55.0 cm) |
| Package 1 Weight | 24.25 lb(US) (11.0 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

| Reach Regulation | REACh Declaration | |
|---------------------------|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | |
| China Rohs Regulation | China RoHS declaration | |
| Environmental Disclosure | Product Environmental Profile | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | |
| Circularity Profile | End of Life Information | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | |

Dimensions Drawings

External Dimensions

With Standard Braking Resistor



- (1) Module for supply voltage
- (2) I/O module
- (3) Standard braking resistor


Dimensions in mm

| W | Н | L |
|-------|-----|-----|
| 132,6 | 217 | 320 |

Dimensions in in.

| W | Н | L |
|------|------|------|
| 5,22 | 8,54 | 12,6 |

Mounting type B




(2) I/O module

(3) Standard braking resistor

| Dimensions in mm | | | |
|------------------|-----|-----|--|
| W | Н | L | |
| 132,6 | 168 | 369 | |

| Dimensions in in. | | | |
|-------------------|------|-------|--|
| W | H L | | |
| 5,22 | 6,61 | 14,53 | |

With External Braking Resistor



(1) Module for supply voltage

- (2) I/O module
- (4) External braking resistor


Dimensions in mm

| W | Н | L |
|-------|-----|-----|
| 132,6 | 217 | 332 |

Dimensions in in.

| W | Н | L |
|------|------|-------|
| 5,22 | 8,54 | 13,07 |

Mounting type D



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor


| | Dime | nsions | in | mm |
|--|------|--------|----|----|
|--|------|--------|----|----|

| W | Н | L |
|-------|-----|-----|
| 132,6 | 180 | 369 |

Dimensions in in.

| W | Н | L |
|------|------|-------|
| 5,22 | 7,09 | 14,53 |

Mounting type E




- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W | Н | L |
|-------|-----|-----|
| 132,6 | 217 | 359 |

| Dimensions in in. | | | | | |
|-------------------|------|-------|--|--|--|
| W | Н | L | | | |
| 5,22 | 8,54 | 14,13 | | | |

Mounting type F



- (1) Module for supply voltage
- (2) I/O module
- (4) External braking resistor

Dimensions in mm

| W | Н | L |
|-------|-------|-----|
| 132,6 | 206,5 | 369 |

Dimensions in in.


| W | Н | L |
|------|------|-------|
| 5,22 | 8,13 | 14,53 |

BMI1003P17A

Performance Curves

Performance Curves

Torque/Speed Curves with 208 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

| | | Power | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power | | 2675 W | 1380 rpm | 18.51 N.m |
| max Cont. Power (Drive) | • | 1223 W | 1620 rpm | 7.21 N.m |

Performance Curves

Torque/Speed Curves with 400 V Three Phases Supply Voltage




- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

| | | Power | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power | | 5328 W | 2760 rpm | 18.44 N.m |
| max Cont. Power (Drive) | • | 2096 W | 3240 rpm | 6.18 N.m |

Performance Curves

Torque/Speed Curves with 480 V Three Phases Supply Voltage



- (X) Speed (rpm)
- (Y) Torque (N.m)
- (1) Motor peak
- (2) Drive peak
- (3) Drive cont
- (4) Motor cont
- (5) Operating point

| | | Power | At Speed | With Torque |
|-------------------------|---|--------|----------|-------------|
| max. Peak Power | | 6454 W | 3360 rpm | 18.34 N.m |
| max Cont. Power (Drive) | • | 1994 W | 3960 rpm | 4.81 N.m |