Product data sheet

Specifications





network module, Modicon M340, EtherNet/IP and Modbus/TCP, 4 x RJ45

BMXNOC0401

Product availability: Stock - Normally stocked in distribution facility

Main

Range Of Product	Modicon M340 automation platform
Product Or Component Type	Ethernet TCP/IP network module
Concept	Transparent Ready
Integrated Connection Type	Ethernet RJ45 10/100 Mbit/s 4 twisted pairs transparent ready class B30
Protective Treatment	TC

Complementary

Communication Service	Bandwidth management Data Editor (via PC terminal) FDR server Rack Viewer SNMP network administrator Modbus TCP I/O Scanner and Messaging Ethernet/IP I/O Scanner and Messaging Embedded 4-port switch RSTP support Port mirroring
Port Ethernet	10BASE-T/100BASE-TX
Memory Usage	Application saving Activating the standard web server
Supply	Internal power supply via rack
Marking	CE
Local Signalling	for processor running (RUN) 1 LED (green) for processor or system fault (ERR) 1 LED (red) for status of Ethernet network (ETH STS) 1 LED (amber) for MS (Module Status) 1 LED (green/red) for NS (Network Status) 1 LED (green/red)
Control Type	Processor or system fault (ERR)
Current Consumption	555 mA 3.3 V DC
Module Format	Standard
Net Weight	0.44 lb(US) (0.2 kg)

Environment

Ambient Air Temperature For Operation	32140 °F (060 °C)
Relative Humidity	1095 % without condensation
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility 2014/34/EU - ATEX directive

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications	CE		
	UL		
	CSA		
	RCM EAC Merchant Navy		
			ATEX zone 2/22
			IECEx zone 2/22
Standards	EN/IEC 61131-2		
	EN/IEC 61010-2-201		
	UL 61010-2-201		
	CSA C22.2 No 61010-2-201		
	IACS E10		
	EN/IEC 61000-6-5, interface type 1 and type 2		
	EN/IEC 61850-3, location G		
	EN/IEC 60079-0		
Environmental Characteristic	Hazardous location class I division 2		

Ordering and shipping details

Category	US1PC3418160
Discount Schedule	PC34
Gtin	3595864083575
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.500 cm)
Package 1 Width	4.33 in (11.000 cm)
Package 1 Length	4.72 in (12.000 cm)
Package 1 Weight	7.72 oz (219.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	8.06 lb(US) (3.656 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.		
Weee			
Weee Circularity Profile			

Product data sheet

Dimensions Drawings

Modules Mounted on Racks

Dimensions



(1) With removable terminal block (cage, screw or spring).

(2) With FCN connector.

(3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81