



### Overview

Model Name	Back UPS PRO BN 1375VA, 10 Outlets, 2 USB Charging Ports, AVR, LCD interface
Includes	USB cable , User Manual , coaxial cable
Standard Lead Time	Usually in Stock
Product Distribution	United States

### Output

Output Power Capacity	810 Watts / 1375 VA
Max Configurable Power (Watts)	810 Watts / 1375 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Connections	(4) NEMA 5-15R (Surge Protection) , (6) NEMA 5-15R (Battery Backup)

### Input

Nominal Input Voltage	120V
Input Frequency	60 Hz +/- 3 Hz
Input Connections	NEMA 5-15P
Cord Length	6 feet (1.83 meters)
Input voltage range for main operations	88 - 139 V
Maximum Input Current	12 A
Input Breaker Capacity	15 A

### Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Typical recharge time	16 hour(s)
Replacement Battery	APCRBC162
RBC Quantity	2

## Communications & Management

Interface Port(s)	USB
Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	1080 Joules
Filtering	Full time multi-pole noise filtering :5% of IEEE surge let-through : zero clamping response time: instantaneous
Data Line Protection	Coaxial cable for CATV/SATV/modem/Audio-Video (coax connector) , RJ45 10/100/1000 Base-T Ethernet protection

## Physical

Maximum Height	10.24 inches (260.0 mm)
Maximum Width	3.94 inches (100.0 mm)
Maximum Depth	14.49 inches (368.0 mm)
Net Weight	22.93 lbs (10.4 kg)
Shipping Weight	28.66 lbs (13.0 kg)
Shipping Height	14.96 inches (380.0 mm)
Shipping Width	9.49 inches (241.0 mm)
Shipping Depth	19.7 inches (500.0 mm)
Master Carton Units	1.0
Master Carton Weight	13.0 kg
Color	Black
SCC Codes	1073130433535 8
Units per Pallet	16.0

## Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 (non-condensing) %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 104 °F (-15 - 40 °C)
Storage Relative Humidity	0 - 95 (non-condensing) %
Storage Elevation	0-10000 feet (0-3000 meters)
Audible noise at 1 meter from surface of unit	45.000 dB

## Conformance

Approvals	ENERGY STAR V2.0 (USA) , FCC Part 15 Class B , NOM , TUV C-US certified
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$250000

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs