Specifications





3-phase stepper motor - 4.8 Nm - shaft \tilde{A}^{\sim} 12mm - L=98mm - w/o brake - conn

BRS39AW661ACA

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,514.11 USD

Main

| Range Compatibility | Lexium SD3 |
|---------------------------|-----------------------|
| Product Or Component Type | Motion control motor |
| Device Short Name | BRS3 |
| Maximum Mechanical Speed | 3000 rpm |
| Motor Type | 3-phase stepper motor |
| Number Of Motor Poles | 6 |
| Supply Voltage Limits | 230 V AC 325 V DC |
| Mounting Support | Flange |
| Motor Flange Size | 3.35 in (85 mm) |
| Length | 5.55 in (141 mm) |
| Centring Collar Diameter | 2.36 in (60 mm) |

Complementary

| Centring Collar Depth | 0.08 in (2 mm) | |
|---------------------------------------|--------------------------|--|
| Number Of Mounting Holes | 4 | |
| Mounting Holes Diameter | 0.26 in (6.5 mm) | |
| Circle Diameter Of The Mounting Holes | 3.90 in (98.99 mm) | |
| Electrical Connection | Connector | |
| Feedback Type | Single turn encoder | |
| Speed Feedback Resolution | 10000 points/turn | |
| Holding Brake | Without | |
| Shaft End | Woodruff key | |
| Second Shaft | Without second shaft end | |
| Shaft Diameter | 0.47 in (12 mm) | |
| Shaft Length | 1.18 in (30 mm) | |
| Nominal Torque | 35.40 lbf.in (4 N.m) | |
| Holding Torque | 42.48 lbf.in (4.8 N.m) | |
| Rotor Inertia | 2.2 kg.cm² | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Resolution | 1.8 °, 0.9 °, 0.72 °, 0.36 °, 0.18 °, 0.09 °, 0.072 °, 0.036 ° step angle 200, 400, 500, 1000, 2000, 4000, 5000, 10000 steps number of full steps per revolution | |
|----------------------------|--|--|
| Accuracy Error | +/- 6 arc min | |
| Maximum Starting Frequency | 5.3 kHz | |
| Line Rated Current | 5.8 A | |
| Resistance | 0.55 Ohm winding) | |
| Time Constant | 9 ms | |
| Maximum Radial Force Fr | 110 N first shaft end) 50 N second shaft end) | |
| Maximum Axial Force Fa | 175 N tensile force) 30 N force pressure) | |
| Service Life In Hours | 20000 h bearing) | |
| Angular Acceleration | 200000 rad/s² | |
| Net Weight | 7.05 lb(US) (3.2 kg) | |

Environment

| Standards | IEC 60072-1 IEC 50347 | |
|---------------------------------------|--|--|
| Type Of Cooling | Natural convection | |
| Ambient Air Temperature For Operation | -13104 °F (-2540 °C) | |
| Ambient Air Temperature For Storage | -13158 °F (-2570 °C) | |
| Operating Altitude | <= 3280.84 ft (1000 m) without power derating | |
| Relative Humidity | 1585 % without condensation | |
| Vibration Resistance | 20 m/s² maximum A IEC 60034-14 | |
| Ip Degree Of Protection | IP56 total except shaft bushing: conforming to IEC 60034-5 IP41 shaft bushing without shaft seal ring: conforming to IEC 60034-5 | |
| Temperature Class | F winding IEC 60034-1 | |

Ordering and shipping details

| Category | US1PC5518284 |
|-------------------|---------------|
| Discount Schedule | PC55 |
| Gtin | 3389119223911 |
| Returnability | No |
| Country Of Origin | DE |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.86 in (22.5 cm) |
| Package 1 Width | 7.68 in (19.5 cm) |
| Package 1 Length | 15.55 in (39.5 cm) |
| Package 1 Weight | 11.02 lb(US) (5.0 kg) |
| Unit Type Of Package 2 | P06 |

| Number Of Units In Package 2 | 12 |
|------------------------------|-------------------------|
| Package 2 Height | 30.31 in (77.0 cm) |
| Package 2 Width | 31.50 in (80.0 cm) |
| Package 2 Length | 23.62 in (60.0 cm) |
| Package 2 Weight | 151.02 lb(US) (68.5 kg) |

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free | |
|----------|----------------------------|-----|
| | Rohs Exemption Information | Yes |
| ② | Pvc Free | |

Certifications & Standards

| Reach Regulation | REACh Declaration | | |
|---------------------------|---|--|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) | | |
| China Rohs Regulation | China RoHS declaration | | |
| Environmental Disclosure | Product Environmental Profile | | |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. | | |
| Circularity Profile | No need of specific recycling operations | | |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov | | |
| | | | |


BRS39AW661ACA

Dimensions Drawings

Dimensions

3-Phase Stepper Motor in Connector Version

in.



3: Motor connection 6 poles

4: Motor connection (optional) 12 poles

Dimensions in mm

| L | Shaft diameter ØW | Centring collar ØZ | Woodruff key DIN 6888 (1) |
|--------------------|-------------------|--------------------|---------------------------|
| 97.5 (+0.6) (-0.8) | 12 h6 | 60 h8 | 4 x 6.5 |


Dimensions in in.

| Difficionio III III. | | | |
|------------------------|-------------------|--------------------|---------------------------|
| L | Shaft diameter ØW | Centring collar ØZ | Woodruff key DIN 6888 (1) |
| 3.84 (+0.023) (-0.031) | 0.47 h6 | 2.36 h8 | 0.16 x 0.25 |

BRS39AW661ACA

Connections and Schema

Wiring Diagram of Encoder Plug on BRS3••



1: Motor housing


| Pin | Designation |
|-----|----------------------|
| 1 | А |
| 2 | A negated |
| 3 | В |
| 4 | B negated |
| 5 | C, I |
| 6 | C negated, I negated |
| 7 | 5 V _{GND} |
| 8 | + 5 |
| 9 | -SENSE |
| 10 | +SENSE |
| 11 | Temperature sensor |
| 12 | Not connected |

BRS39AW661ACA

Performance Curves

Torque Characteristics

Measurement at 1000 Steps/Revolution, Nominal Voltage DC Bus $\mathbf{U_N}$ and Phase Current $\mathbf{I_N}$



M: Torque in Nm

n: Speed in rpm

f: Frequency in kHz

J: Rotor inertia in kg.cm²

1: Pull-out torque

2: Pull-in torque

3: Maximum load inertia