


Product data sheet

Specifications



AC servo motor BSH, Lexium 05,
1.1N.m, 3000rpm, untapped shaft,
with brake, IP50

BSH0703P02F1A

⚠ Discontinued on: Oct 9, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Product Or Component Type	Servo motor
Device Short Name	BSH
Maximum Mechanical Speed	8000 rpm
Continuous Stall Torque	25.05 lbf.in (2.83 N.m) LXM15LD21M3, 230 V, single phase 9.74 lbf.in (1.1 N.m) LXM15LU60N4, 480 V, three phase 9.74 lbf.in (1.1 N.m) LXM15LU60N4, 400 V, three phase 13.28 lbf.in (1.5 N.m) LXM15LU60N4, 230 V, three phase 19.74 lbf.in (2.23 N.m) LXM15LD13M3, 230 V, three phase 21.24 lbf.in (2.4 N.m) LXM15LD10N4, 230 V, three phase 21.24 lbf.in (2.4 N.m) LXM15LD10N4, 400 V, three phase 21.24 lbf.in (2.4 N.m) LXM15LD10N4, 480 V, three phase 25.05 lbf.in (2.83 N.m) LXM15LD17N4, 230 V, three phase 25.05 lbf.in (2.83 N.m) LXM15LD17N4, 400 V, three phase 25.05 lbf.in (2.83 N.m) LXM15LD17N4, 480 V, three phase 25.05 lbf.in (2.83 N.m) LXM15LD21M3, 230 V, three phase 24.78 lbf.in (2.8 N.m) LXM05AD17M2, 200...240 V, single phase 24.78 lbf.in (2.8 N.m) LXM05AD17M3X, 200...240 V, three phase 24.78 lbf.in (2.8 N.m) LXM05AD22N4, 380...480 V, three phase 24.78 lbf.in (2.8 N.m) LXM05AD28M2, 200...240 V, single phase 24.78 lbf.in (2.8 N.m) LXM05BD17M2, 200...240 V, single phase 24.78 lbf.in (2.8 N.m) LXM05BD17M3X, 200...240 V, three phase 24.78 lbf.in (2.8 N.m) LXM05BD22N4, 380...480 V, three phase 24.78 lbf.in (2.8 N.m) LXM05BD28M2, 200...240 V, single phase 24.78 lbf.in (2.8 N.m) LXM05CD17M2, 200...240 V, single phase 24.78 lbf.in (2.8 N.m) LXM05CD17M3X, 200...240 V, three phase 24.78 lbf.in (2.8 N.m) LXM05CD22N4, 380...480 V, three phase 24.78 lbf.in (2.8 N.m) LXM05CD28M2, 200...240 V, single phase 27.44 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 400 V, three phase 27.44 lbf.in (3.1 N.m) LXM32.D18N4 6 A, 480 V, three phase

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Peak Stall Torque	53.02 lbf.in (5.99 N.m) LXM15LD21M3, 230 V, single phase
	63.37 lbf.in (7.16 N.m) LXM05AD17M2, 200...240 V, single phase
	91.16 lbf.in (10.3 N.m) LXM05AD28M2, 200...240 V, single phase
	63.37 lbf.in (7.16 N.m) LXM05BD17M2, 200...240 V, single phase
	91.16 lbf.in (10.3 N.m) LXM05BD28M2, 200...240 V, single phase
	63.37 lbf.in (7.16 N.m) LXM05CD17M2, 200...240 V, single phase
	91.16 lbf.in (10.3 N.m) LXM05CD28M2, 200...240 V, single phase
	29.21 lbf.in (3.3 N.m) LXM15LU60N4, 480 V, three phase
	29.21 lbf.in (3.3 N.m) LXM15LU60N4, 400 V, three phase
	29.21 lbf.in (3.3 N.m) LXM15LU60N4, 230 V, three phase
	53.10 lbf.in (6 N.m) LXM15LD13M3, 230 V, three phase
	46.91 lbf.in (5.3 N.m) LXM15LD10N4, 230 V, three phase
	46.91 lbf.in (5.3 N.m) LXM15LD10N4, 400 V, three phase
	46.91 lbf.in (5.3 N.m) LXM15LD10N4, 480 V, three phase
	68.24 lbf.in (7.71 N.m) LXM15LD17N4, 230 V, three phase
	68.24 lbf.in (7.71 N.m) LXM15LD17N4, 400 V, three phase
	68.24 lbf.in (7.71 N.m) LXM15LD17N4, 480 V, three phase
	82.13 lbf.in (9.28 N.m) LXM15LD21M3, 230 V, three phase
	63.37 lbf.in (7.16 N.m) LXM05AD17M3X, 200...240 V, three phase
	77.44 lbf.in (8.75 N.m) LXM05AD22N4, 380...480 V, three phase
	63.37 lbf.in (7.16 N.m) LXM05BD17M3X, 200...240 V, three phase
	77.44 lbf.in (8.75 N.m) LXM05BD22N4, 380...480 V, three phase
	63.37 lbf.in (7.16 N.m) LXM05CD17M3X, 200...240 V, three phase
	77.44 lbf.in (8.75 N.m) LXM05CD22N4, 380...480 V, three phase
	100.01 lbf.in (11.3 N.m) LXM32.D18N4 6 A, 400 V, three phase
	100.01 lbf.in (11.3 N.m) LXM32.D18N4 6 A, 480 V, three phase
Nominal Output Power	750 W LXM05AD17M2, 200...240 V, single phase
	750 W LXM05AD28M2, 200...240 V, single phase
	750 W LXM05BD17M2, 200...240 V, single phase
	750 W LXM05BD28M2, 200...240 V, single phase
	750 W LXM05CD17M2, 200...240 V, single phase
	750 W LXM05CD28M2, 200...240 V, single phase
	750 W LXM15LD21M3, 230 V, single phase
	1250 W LXM15LD10N4, 400 V, three phase
	1300 W LXM15LD17N4, 400 V, three phase
	1400 W LXM15LD17N4, 480 V, three phase
	1500 W LXM15LD10N4, 480 V, three phase
	350 W LXM15LU60N4, 230 V, three phase
	700 W LXM15LD13M3, 230 V, three phase
	700 W LXM15LU60N4, 400 V, three phase
	750 W LXM05AD17M3X, 200...240 V, three phase
	750 W LXM05AD22N4, 380...480 V, three phase
	750 W LXM05BD17M3X, 200...240 V, three phase
	750 W LXM05BD22N4, 380...480 V, three phase
	750 W LXM05CD17M3X, 200...240 V, three phase
	750 W LXM05CD22N4, 380...480 V, three phase
	750 W LXM15LD10N4, 230 V, three phase
	750 W LXM15LD17N4, 230 V, three phase
	750 W LXM15LD21M3, 230 V, three phase
	950 W LXM15LU60N4, 480 V, three phase
	1300 W LXM32.D18N4 6 A, 400 V, three phase
	1300 W LXM32.D18N4 6 A, 480 V, three phase

Nominal Torque	21.24 lbf.in (2.4 N.m) LXM05AD17M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM05AD28M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM05BD17M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM05BD28M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM05CD17M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM05CD28M2, 200...240 V, single phase
	21.24 lbf.in (2.4 N.m) LXM15LD21M3, 230 V, single phase
	9.91 lbf.in (1.12 N.m) LXM15LU60N4, 230 V, three phase
	9.91 lbf.in (1.12 N.m) LXM15LU60N4, 400 V, three phase
	9.91 lbf.in (1.12 N.m) LXM15LU60N4, 480 V, three phase
	15.93 lbf.in (1.8 N.m) LXM15LD10N4, 480 V, three phase
	17.35 lbf.in (1.96 N.m) LXM15LD17N4, 480 V, three phase
	17.70 lbf.in (2 N.m) LXM15LD10N4, 400 V, three phase
	17.70 lbf.in (2 N.m) LXM15LD17N4, 400 V, three phase
	19.74 lbf.in (2.23 N.m) LXM15LD13M3, 230 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05AD17M3X, 200...240 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05AD22N4, 380...480 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05BD17M3X, 200...240 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05BD22N4, 380...480 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05CD17M3X, 200...240 V, three phase
	21.24 lbf.in (2.4 N.m) LXM05CD22N4, 380...480 V, three phase
	21.24 lbf.in (2.4 N.m) LXM15LD10N4, 230 V, three phase
	21.24 lbf.in (2.4 N.m) LXM15LD17N4, 230 V, three phase
	21.24 lbf.in (2.4 N.m) LXM15LD21M3, 230 V, three phase
	21.60 lbf.in (2.44 N.m) LXM32.D18N4 6 A, 400 V, three phase
	21.60 lbf.in (2.44 N.m) LXM32.D18N4 6 A, 480 V, three phase
Nominal Speed	3000 rpm LXM15LD13M3, 230 V, three phase
	3000 rpm LXM05AD17M2, 200...240 V, single phase
	3000 rpm LXM05BD17M2, 200...240 V, single phase
	3000 rpm LXM05CD17M2, 200...240 V, single phase
	3000 rpm LXM05AD17M3X, 200...240 V, three phase
	3000 rpm LXM05BD17M3X, 200...240 V, three phase
	3000 rpm LXM05CD17M3X, 200...240 V, three phase
	3000 rpm LXM15LU60N4, 230 V, three phase
	8000 rpm LXM15LD10N4, 480 V, three phase
	8000 rpm LXM15LU60N4, 480 V, three phase
	3000 rpm LXM15LD10N4, 230 V, three phase
	6000 rpm LXM15LD10N4, 400 V, three phase
	3000 rpm LXM05AD28M2, 200...240 V, single phase
	3000 rpm LXM05BD28M2, 200...240 V, single phase
	3000 rpm LXM05CD28M2, 200...240 V, single phase
	3000 rpm LXM15LD21M3, 230 V, single phase
	3000 rpm LXM05AD22N4, 380...480 V, three phase
	3000 rpm LXM05BD22N4, 380...480 V, three phase
	3000 rpm LXM05CD22N4, 380...480 V, three phase
	3000 rpm LXM15LD17N4, 230 V, three phase
	3000 rpm LXM15LD21M3, 230 V, three phase
	6000 rpm LXM15LD17N4, 400 V, three phase
	6000 rpm LXM15LU60N4, 400 V, three phase
	7000 rpm LXM15LD17N4, 480 V, three phase
	5000 rpm LXM32.D18N4 6 A, 400 V, three phase
	5000 rpm LXM32.D18N4 6 A, 480 V, three phase

Product Compatibility	LXM05AD17M2 200...240 V single phase LXM05AD28M2 200...240 V single phase LXM05BD17M2 200...240 V single phase LXM05BD28M2 200...240 V single phase LXM05CD17M2 200...240 V single phase LXM05CD28M2 200...240 V single phase LXM15LD21M3 230 V single phase LXM15LU60N4 230 V three phase LXM15LD13M3 230 V three phase LXM15LU60N4 400 V three phase LXM15LU60N4 480 V three phase LXM15LD10N4 400 V three phase LXM05AD17M3X 200...240 V three phase LXM05BD17M3X 200...240 V three phase LXM05CD17M3X 200...240 V three phase LXM15LD10N4 230 V three phase LXM15LD10N4 480 V three phase LXM15LD21M3 230 V three phase LXM15LD17N4 230 V three phase LXM05AD22N4 380...480 V three phase LXM05BD22N4 380...480 V three phase LXM05CD22N4 380...480 V three phase LXM15LD17N4 400 V three phase LXM15LD17N4 480 V three phase LXM32.D18N4 400 V three phase LXM32.D18N4 480 V three phase
Shaft End	Untapped
Ip Degree Of Protection	IP50 standard
Speed Feedback Resolution	131072 points/turn x 4096 turns
Holding Brake	With
Mounting Support	International standard flange
Electrical Connection	Straight connectors

Complementary

Range Compatibility	Lexium 05 Lexium 32 Lexium 15
Supply Voltage Max	480 V
Phase	Three phase
Continuous Stall Current	4.1 A
Maximum Continuous Power	1.7 W
Maximum Current Irms	15.2 A LXM15LD13M3 15.2 A LXM15LD21M3 15.2 A LXM15LD17N4 15.2 A LXM15LU60N4 15.2 A LXM15LD10N4 17 A LXM05AD17M2 17 A LXM05AD28M2 17 A LXM05AD17M3X 17 A LXM05AD22N4 17 A LXM05BD17M2 17 A LXM05BD28M2 17 A LXM05BD17M3X 17 A LXM05BD22N4 17 A LXM05CD17M2 17 A LXM05CD28M2 17 A LXM05CD17M3X 17 A LXM05CD22N4 17 A LXM32.D18N4
Maximum Permanent Current	17 A
Switching Frequency	8 kHz
Second Shaft	Without second shaft end

Shaft Diameter	0.55 in (14 mm)
Shaft Length	1.18 in (30 mm)
Feedback Type	Multiturn SinCos Hiperface
Holding Torque	26.55 lbf.in (3 N.m) holding brake
Motor Flange Size	2.76 in (70 mm)
Number Of Motor Stacks	3
Torque Constant	0.78 N.m/A 248 °F (120 °C)
Back Emf Constant	49 V/krpm 248 °F (120 °C)
Number Of Motor Poles	6
Rotor Inertia	0.81 kg.cm²
Stator Resistance	2.7 Ohm 68 °F (20 °C)
Stator Inductance	13 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.82 ms 68 °F (20 °C)
Maximum Radial Force Fr	400 N 6000 rpm 430 N 5000 rpm 460 N 4000 rpm 510 N 3000 rpm 580 N 2000 rpm 730 N 1000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	12 W
Type Of Cooling	Natural convection
Length	10.00 in (254 mm)
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Circle Diameter Of The Mounting Holes	3.23 in (82 mm)
Net Weight	8.38 lb(US) (3.8 kg)

Ordering and shipping details

Category	US1PC5318282
Discount Schedule	PC53
Gtin	3389118137189
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.84 in (12.3 cm)
Package 1 Width	5.04 in (12.8 cm)
Package 1 Length	14.84 in (37.7 cm)

Package 1 Weight	8.93 lb(US) (4.05 kg)
------------------	-----------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
b: Power supply for servo motor encoder
(1) M4 screw
(2) Shaft end, keyed slot (optional)
Dimensions in mm

Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	c3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2									
39.5	25.5	39.5	39.5	220	254	30	20	5	5 N9	3 ^{+0.1} ₀	14 k6	M5 x 12.5

Dimensions in in.


Straight connectors		Rotatable angled connectors		c (without brake)	c (with brake)	c1	c2	c3	h	h1	Ø	Ø1 for screws
b1	b2	b1	b2									
1.55	1.00	1.55	1.55	8.66	10.00	1.18	0.78	0.19	0.20 N9	0.12 ^{+0.004} ₀	0.55 k6	M5 x 0.49

Performance Curves

400 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive




- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque

480 V 3-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D18N4 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque