## Product data sheet

Specifications

Green Premium<sup>®</sup>



# AC servo motor BSH, Lexium 05, 2.12N.m, 6000rpm, keyed shaft, without brake, IP65

BSH0702T32A1A

Discontinued on: Oct 9, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Product Or Component Type	Servo motor							
Device Short Name	BSH							
Maximum Mechanical Speed	8000 rpm							
Continuous Stall Torque	19.47 lbf.in (2.2 N.m) LXM32.D30M2 10 A, 115 V, single phase 18.76 lbf.in (2.12 N.m) LXM05AD17M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05BD17M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17M2, 200240 V, single phase 19.47 lbf.in (2.12 N.m) LXM05CD17M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05AD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05AD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05AD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05BD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05BD28M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD128M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17F1, 110120 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17F1, 11020V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD128M2, 200240 V, single phase 18.76 lbf.in (2.12 N.m) LXM05CD17M4, 230 V, three phase 18.76 lbf.in (2.12 N.m) LXM15LD17N4, 230 V, three phase 18.76 lbf.in (2.12 N.m) LXM05AD42M3X, 200240 V, three phase 18.76 lbf.in (2.12 N.m) LXM05AD42M3X, 200240 V, three phase							
Peak Stall Torque	18.76 lbf.in (2.12 N.m) LXM05CD42M3X, 200240 V, three phase 53.99 lbf.in (6.1 N.m) LXM32.D30M2 10 A, 115 V, single phase							
	63.73 lbf.in (7.2 N.m) LXM32.D18M2 6 A, 230 V, single phase 36.64 lbf.in (4.14 N.m) LXM05AD17F1, 110120 V, single phase 36.64 lbf.in (4.14 N.m) LXM05AD17M2, 200240 V, single phase 36.64 lbf.in (4.14 N.m) LXM05BD17F1, 110120 V, single phase 36.64 lbf.in (4.14 N.m) LXM05BD17F1, 110120 V, single phase 36.64 lbf.in (4.14 N.m) LXM05CD17F1, 110120 V, single phase 36.64 lbf.in (4.14 N.m) LXM05CD17F1, 110120 V, single phase 36.64 lbf.in (4.14 N.m) LXM05CD17F1, 110120 V, single phase 36.64 lbf.in (6.14 N.m) LXM05CD17F1, 200240 V, single phase 60.18 lbf.in (6.8 N.m) LXM05D28M2, 200240 V, single phase 60.18 lbf.in (6.8 N.m) LXM05D28M2, 200240 V, single phase 39.56 lbf.in (6.8 N.m) LXM05CD28M2, 200240 V, single phase 39.56 lbf.in (4.47 N.m) LXM15LD17N4, 230 V, three phase 48.24 lbf.in (5.45 N.m) LXM05AD42M3X, 200240 V, three phase 60.18 lbf.in (6.8 N.m) LXM05AD42M3X, 200240 V, three phase 60.18 lbf.in (6.8 N.m) LXM05CD42M3X, 200240 V, three phase 60.18 lbf.in (6.8 N.m) LXM05CD42M3X, 200240 V, three phase							
Nominal Output Power	550 W LXM32.D30M2 10 A, 115 V, single phase 600 W LXM05AD17M2, 200240 V, single phase 600 W LXM05BD17M2, 200240 V, single phase 600 W LXM05CD17M2, 200240 V, single phase 570 W LXM05AD17F1, 110120 V, single phase 570 W LXM05AD17F1, 110120 V, single phase 570 W LXM05BD17F1, 110120 V, single phase 600 W LXM05AD28M2, 200240 V, single phase 600 W LXM05AD28M2, 200240 V, single phase 600 W LXM05D2028M2, 200240 V, single phase 600 W LXM05D2028M2, 200240 V, single phase 950 W LXM32.D18M2 6 A, 230 V, single phase 1000 W LXM15LD17N4, 230 V, three phase 600 W LXM05AD42M3X, 200240 V, three phase 600 W LXM05BD42M3X, 200240 V, three phase 600 W LXM05BD42M3X, 200240 V, three phase 600 W LXM05BD42M3X, 200240 V, three phase							

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Life Is On Schneider

Nominal Torque	18.32 lbf.in (2.07 N.m) LXM32.D30M2 10 A, 115 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05AD17M2, 200240 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05BD17M2, 200240 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05CD17M2, 200240 V, single phase
	16.20 lbf.in (1.83 N.m) LXM05AD17F1, 110120 V, single phase
	16.20 lbf.in (1.83 N.m) LXM05BD17F1, 110120 V, single phase
	16.20 lbf.in (1.83 N.m) LXM05CD17F1, 110120 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05AD28M2, 200240 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05BD28M2, 200240 V, single phase
	16.82 lbf.in (1.9 N.m) LXM05CD28M2, 200240 V, single phase
	15.93 lbf.in (1.8 N.m) LXM32.D18M2 6 A, 230 V, single phase
	14.69 lbf.in (1.66 N.m) LXM15LD17N4, 230 V, three phase
	14.69 lbf.in (1.66 N.m) LXM15LD21M3, 230 V, three phase
	16.82 lbf.in (1.9 N.m) LXM05AD42M3X, 200240 V, three phase
	16.82 lbf.in (1.9 N.m) LXM05BD42M3X, 200240 V, three phase 16.82 lbf.in (1.9 N.m) LXM05CD42M3X, 200240 V, three phase
Nominal Speed	2500 rpm LXM32.D30M2 10 A, 115 V, single phase
	3000 rpm LXM05AD17F1, 110120 V, single phase
	3000 rpm LXM05BD17F1, 110120 V, single phase
	3000 rpm LXM05CD17F1, 110120 V, single phase
	3000 rpm LXM05AD17M2, 200240 V, single phase
	3000 rpm LXM05BD17M2, 200240 V, single phase
	3000 rpm LXM05CD17M2, 200240 V, single phase
	3000 rpm LXM05AD28M2, 200240 V, single phase
	3000 rpm LXM05BD28M2, 200240 V, single phase
	3000 rpm LXM05CD28M2, 200240 V, single phase
	5000 rpm LXM32.D18M2 6 A, 230 V, single phase
	3000 rpm LXM05AD42M3X, 200240 V, three phase
	3000 rpm LXM05BD42M3X, 200240 V, three phase
	3000 rpm LXM05CD42M3X, 200240 V, three phase
	6000 rpm LXM15LD17N4, 230 V, three phase
	6000 rpm LXM15LD21M3, 230 V, three phase
Product Compatibility	LXM05AD17F1 110120 V single phase
	LXM05AD17M2 200240 V single phase
	LXM05AD28M2 200240 V single phase
	LXM05BD17F1 110120 V single phase
	LXM05BD17M2 200240 V single phase
	LXM05BD28M2 200240 V single phase
	LXM05CD17F1 110120 V single phase
	LXM05CD17M2 200240 V single phase
	LXM05CD28M2 200240 V single phase
	LXM32.D30M2 115 V single phase
	LXM32.D18M2 230 V single phase
	LXM15LD21M3 230 V three phase
	LXM05AD42M3X 200240 V three phase
	LXM05BD42M3X 200240 V three phase
	LXM05CD42M3X 200240 V three phase
	LXM15LD17N4 230 V three phase
Shaft End	Keyed
p Degree Of Protection	IP65 standard
	IP67 with IP67 kit
Speed Feedback Resolution	131072 points/turn x 4096 turns
Holding Brake	Without
Mounting Support	International standard flange
Electrical Connection	Straight connectors
0	
Complementary	
Range Compatibility	Levium 05

Range Compatibility	Lexium 05 Lexium 15 Lexium 32
Supply Voltage Max	480 V
Phase	Three phase
Continuous Stall Current	4.9 A
Maximum Continuous Power	1.51 W

Maximum Current Irms	20.6 A LXM15LD21M3
	20.6 A LXM15LD17N4
	19.9 A LXM05AD17F1 19.9 A LXM05AD17M2
	19.9 A LXM05AD28M2
	19.9 A LXM05AD42M3X
	19.9 A LXM05BD17F1
	19.9 A LXM05BD17M2
	19.9 A LXM05BD28M2
	19.9 A LXM05BD42M3X
	19.9 A LXM05CD17F1
	19.9 A LXM05CD17M2 19.9 A LXM05CD28M2
	19.9 A LXM05CD42Miz
	15 A LXM32.D30M2
	18 A LXM32.D18M2
Maximum Permanent Current	19.9 A
Switching Frequency	8 kHz
Second Shaft	Without second shaft end
Shaft Diameter	0.43 in (11 mm)
Shaft Length	0.91 in (23 mm)
Key Width	0.71 in (18 mm)
Feedback Type	Multiturn SinCos Hiperface
Motor Flange Size	2.76 in (70 mm)
Number Of Motor Stacks	2
Torque Constant	0.45 N.m/A 248 °F (120 °C)
Back Emf Constant	28 V/krpm 248 °F (120 °C)
Number Of Motor Poles	6
Rotor Inertia	0.41 kg.cm <sup>2</sup>
Stator Resistance	1.5 Ohm 68 °F (20 °C)
Stator Inductance	6.7 mH 68 °F (20 °C)
Stator Electrical Time Constant	4.47 ms 68 °F (20 °C)
Maximum Radial Force Fr	390 N 6000 rpm
	410 N 5000 rpm
	450 N 4000 rpm
	490 N 3000 rpm 560 N 2000 rpm
	710 N 1000 rpm
Maximum Axial Force Fa	0.2 x Fr
Type Of Cooling	Natural convection
Length	7.36 in (187 mm)
Centring Collar Diameter	2.36 in (60 mm)
Centring Collar Depth	0.10 in (2.5 mm)
Number Of Mounting Holes	4
Mounting Holes Diameter	0.22 in (5.5 mm)
Mounting Holes Diameter Circle Diameter Of The Mounting Holes	0.22 in (5.5 mm) 3.23 in (82 mm)

## Ordering and shipping details

Category

US1PC5318282

Discount Schedule	PC53
Gtin	3389118136762
Returnability	No
Country Of Origin	DE

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.84 in (12.3 cm)
Package 1 Width	5.04 in (12.8 cm)
Package 1 Length	14.84 in (37.7 cm)
Package 1 Weight	6.17 lb(US) (2.8 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information
Yes


## **Certifications & Standards**

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

#### **Dimensions Drawings**

#### Servo Motors Dimensions

#### **Example with Straight Connectors**



a: Power supply for servo motor brakeb: Power supply for servo motor encoder

(1) M4 screw

(2) Shaft end, keyed slot (optional)

Dimensions in mm

Straight Rotatable angled connectors connectors		c (without c (with brake) brake)		c1 c2		c3	h	h1	ø	Ø1 for		
b1	b2	b1	b2	brake)	Drake)							screws
39.5	25.5	39.5	39.5	187	213	23	18	2.5	4 N9	2.5 <sup>+0.1</sup> 0	11 k6	M4 x 10

Dimensions in in.


connec	Straight connectors		ole tors	c (without brake)	c (with brake)	c1	c2	c3	h	h1	ø	Ø1 for screws
b1	b2	b1	b2	,								
1.55	1.00	1.55	1.55	7.36	8.38	0.90	0.70	0.09	0.16 N9	0.01 <sup>+0.004</sup> 0	0.43 k6	M4 x 0.39

#### Performance Curves

#### 115 V Single-Phase Supply Voltage

#### **Torque/Speed Curves**

Servo motor with LXM32•D30M2 servo drive



 ${\bf X}$  Speed in rpm

Y Torque in Nm


1 Peak torque

2 Continuous torque

#### 230 V Single-Phase Supply Voltage

#### Torque/Speed Curves

Servo motor with LXM32•D18M2 servo drive



X Speed in rpm

Y Torque in Nm

1 Peak torque

2 Continuous torque