

# BV4T007J

TeSys BV4 motor circuit protector, inst trip, 7A, 3P, EverLink lugs, hi fault

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 500.00 USD



## Main

Range	TeSys
Product name	TeSys BV4
Device short name	BV4
Product or component type	Motor Circuit Protector
Device application	Motor
Performance level	High performance
Poles description	3P
Utilisation category	Category A
Trip unit technology	Magnetic
Protection type	Short-circuit
Line Rated Current	7 A 104 °F (40 °C)
Magnetic setting range	42...98 A 104 °F (40 °C)
Control type	Toggle

## Complementary

[Ue] rated operational voltage	600Y/347 V AC 50/60 Hz
Mounting mode	By clips By screws
Mounting support	75 mm symmetrical DIN rail 35 mm symmetrical DIN rail Plate
Mechanical durability	40000 cycles
Electrical durability	40000 cycles AC-3 440 V In/2 40000 cycles AC-3 440 V In
Local signalling	Presence of auxiliary contacts flag green)
Number of slots	1 alarm switch fault signalling contact, plug-in 1 voltage release electrical remote tripping, plug-in 1 auxiliary switch open/close contact, plug-in

Connection pitch	1.06 in (27 mm)
Electrical Connection	2 EverLink BTR screw connectors 0.00...0.11 in <sup>2</sup> (1.5...70 mm <sup>2</sup> ) AWG 14...AWG 2/0), solid copper 2 EverLink BTR screw connectors 0.00...0.08 in <sup>2</sup> (1.5...50 mm <sup>2</sup> ) AWG 6...AWG 1/0), flexible copper
Tightening torque	44.25 lbf.in (5 N.m) 0.02 in <sup>2</sup> (10 mm <sup>2</sup> ) AWG 8) 79.66 lbf.in (9 N.m) 0.02 in <sup>2</sup> (16 mm <sup>2</sup> ) AWG 6)
Wire stripping length	0.79 in (20 mm)
Height	6.38 in (162 mm)
Width	3.19 in (81 mm)
Depth	4.57 in (116 mm)
Net weight	3.31 lb(US) (1.5 kg)
Quantity per set	1
Color	Grey RAL 7016)

## Environment

Standards	CSA C22.2 No 5 UL 489
Product certifications	CSA UL
IP degree of protection	IP40 front face IEC 60529
IK degree of protection	IK07 IEC 62262
Mechanical robustness	Vibrations +/- 1 mm 2...13.2 Hz IEC 60068-2-6 Vibrations 0.7 gn 13.2...100 Hz IEC 60068-2-6 Shocks 15 gn 11 ms IEC 60068-2-27
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-58...185 °F (-50...85 °C)
Operating altitude	6561.68 ft (2000 m) without derating > 2000...5000 m with derating

## Ordering and shipping details

Category	01124 - TESYS BV4 MOTOR CIRCUIT PROTECTORS
Discount Schedule	I11
GTIN	03606489503666
Package weight(Lbs)	1.54 kg (3.4 lb(US))
Returnability	Yes
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: which is known to the State of California to cause Not determined harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.