

CA2KN225F7

TeSys K control relay - 2 NO + 2 NC - \leq 690 V -
110 V AC coil

Price* : 35.50 USD



CA2KN225F7 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA2K
Contacteur application	Control circuit
Utilisation category	AC-15 DC-13
Pole contact composition	2 NO + 2 NC
System Voltage	\leq 690 V \leq 400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz

Complementary

[Ith] conventional free air thermal current	10 A at \leq 122 °F (50 °C)
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C
Mounting support	Plate Rail
Connections - terminals	Solder pins 1.5 x 0.9 mm
Control circuit voltage limits	0.8...1.15 Uc at 122 °F (50 °C) operational 0.2...0.75 Uc at 122 °F (50 °C) drop-out
Operating time	10...20 ms coil de-energisation and NO opening 5...15 ms coil energisation and NC opening 10...20 ms coil energisation and NO closing 15...25 ms coil de-energisation and NC closing
Mechanical durability	10 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms

Inrush power in VA	30 VA at 68 °F (20 °C)
Hold-in power consumption in VA	4.5 VA at 68 °F (20 °C)
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.02 in (0.5 mm)
Insulation resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Product weight	0.46 lb(US) (0.21 kg)

Environment

Standards	BS 5424 IEC 60947 VDE 0660 NF C 63-140
Product certifications	CSA UL
IP degree of protection	IP2x
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27

Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
Nbr. of units in pkg.	1
Package weight(Lbs)	0.46000000000000002
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------