

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Motor Voltage	480 V - AC at 60 Hz
Reactive power rating	1200 kvar
Operating mode	Automatic & transient free
Range of product	VarSet
Device short name	Varset Fast
Product or component type	Capacitor bank
Controller type	Varplus Logic VPL12 Modbus
Capacitor technology	VarPlus Can + Detuned reactor
Accessibility for operation	Front
Colour	ASA 49 (grey)

Complementary

Network pollution level	Low polluted
[THDv] Total Harmonic Distortion	0...5 %
THDI	0...8 %
Tuning factor	4.2
Tuning frequency	252 Hz
Power per step	150 kvar
Step composition	8x150
Location of connection	Top
Internal voltage transformer	480/120 V
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours)
Protection type	Circuit breaker protection
Breaking capacity	65 kA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Control type	Rotary handle
Maximum weight	5092.68 lb(US) (2310 kg)
Height	2324 mm
Width	2286 mm
Depth	36.02 in (915 mm)
Mounting location	Indoor

Environment

Standards	CSA C22.2 No 190-M1985
NEMA degree of protection	NEMA 1
Mechanical degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 6561.68 ft (2000 m)
Ambient air temperature for operation	14...104 °F (-10...40 °C)
Average ambient air temperature for operation	Annual: 30 °C

Ordering and shipping details

Category	00087 - VARSET AT6000 CTO LV CAP BANK (CTO)
Discount Schedule	DE2C
Nbr. of units in pkg.	1
Package weight(Lbs)	4300
Returnability	N