



Price\* : 36.20 USD



## Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA2K
Contactur application	Control circuit
Utilisation category	DC-13 AC-15
Pole contact composition	3 NO + 1 NC
System Voltage	≤ 690 V ≤ 400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	230...240 V AC 50/60 Hz

## Complementary

[Ith] conventional free air thermal current	10 A at ≤ 122 °F (50 °C)
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C
Mounting support	Rail Plate
Connections - terminals	Screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) - cable stiffness: solid Screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (1.5...4 mm <sup>2</sup> ) - cable stiffness: solid Screw clamp terminals 2 cable(s) 0...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable(s) 0...0.01 in <sup>2</sup> (0.75...4 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable(s) 0...0 in <sup>2</sup> (0.34...1.5 mm <sup>2</sup> ) - cable stiffness: flexible - with cable end

	Screw clamp terminals 2 cable(s) 0...0 in <sup>2</sup> (0.34...1.5 mm <sup>2</sup> ) - cable stiffness: flexible - without cable end
Tightening torque	11.5 lbf.in (1.3 N.m) - on screw clamp terminals - with screwdriver Philips No 2 0.24 in (6 mm) 11.5 lbf.in (1.3 N.m) - on screw clamp terminals - with screwdriver flat Ø 6 mm
Control circuit voltage limits	0.8...1.15 Uc at 122 °F (50 °C) operational 0.2...0.75 Uc at 122 °F (50 °C) drop-out
Operating time	10...20 ms coil de-energisation and NO opening 5...15 ms coil energisation and NC opening 10...20 ms coil energisation and NO closing 15...25 ms coil de-energisation and NC closing
Mechanical durability	10 Mcycles
Operating rate	10000 cyc/h
Immunity to microbreaks	2 ms
Inrush power in VA	30 VA at 68 °F (20 °C)
Hold-in power consumption in VA	4.5 VA at 68 °F (20 °C)
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.02 in (0.5 mm)
Insulation resistance	> 10 MOhm
Height	2.28 in (58 mm)
Width	1.77 in (45 mm)
Depth	2.24 in (57 mm)
Product weight	0.4 lb(US) (0.18 kg)

## Environment

Standards	BS 5424 IEC 60947 VDE 0660 NF C 63-140
Product certifications	UL CSA
IP degree of protection	IP2x
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-13...122 °F (-25...50 °C)
Ambient air temperature for storage	-58...176 °F (-50...80 °C)
Operating altitude	6561.68 ft (2000 m) without derating
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27

## Ordering and shipping details

Category	22371 - RELAYS, CONTROL
Discount Schedule	I12
GTIN	00785901776796
Nbr. of units in pkg.	1
Package weight(Lbs)	0.39000000000000001
Returnability	Y
Country of origin	ID

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0640 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH	<a href="#">Reference not containing SVHC above the threshold</a> <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------