



Overview

Model Name	Power Saving Back-UPS XS 1300
Includes	USB cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	United States

Output

Output Power Capacity	780 Watts / 1300 VA
Max Configurable Power (Watts)	780 Watts / 1300 VA
Nominal Output Voltage	120V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Output Frequency (sync to mains)	Line Interactive
Waveform Type	Stepped approximation to a sinewave
Output Connections	(5) NEMA 5-15R (Battery Backup) , (5) NEMA 5-15R (Surge Protection)
Bypass	Built-in Bypass

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	NEMA 5-15P
Cord Length	6 feet (1.83 meters)

Batteries & Runtime

Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Included Battery Modules	1
Typical recharge time	16 hour(s)
Replacement Battery	APCRBC123
RBC Quantity	1

Communications & Management

Interface Port(s)	USB
-------------------	-----

Control panel	Multi-function LCD status and control console
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	354 Joules
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449
Data Line Protection	Cable modem / Video protection , RJ-45 Modem/Fax protection (two wire single line) , RJ45 10/100 Base-T Ethernet protection

Physical

Maximum Height	11.85 inches (301.0 mm)
Maximum Width	4.41 inches (112.0 mm)
Maximum Depth	15.04 inches (382.0 mm)
Net Weight	23.1 lbs (10.5 kg)
Shipping Weight	28.27 lbs (12.85 kg)
Shipping Height	15.24 inches (387.0 mm)
Shipping Width	9.37 inches (238.0 mm)
Shipping Depth	19.21 inches (488.0 mm)
Master Carton Units	1.0
Color	Black
SCC Codes	1073130426838 0
Units per Pallet	16.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-30000 feet (0-9000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)
Audible noise at 1 meter from surface of unit	45.000 dB

Conformance

Approvals	California (CEC) Battery Charger , TUV , UL Listed
Standard warranty	3 years repair or replace
Equipment protection policy	Lifetime : \$150000

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs